



PANDUIT PART NUMBER	WEIGHT
FR12ACB12 FR12ACB12M	4.29 LB/EACH (1947g/EACH)



NOTES:

- SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE PACKAGE QUANTITY.
- THE FIBERRUNNER 12x4 QUIKLOCK ADJUSTABLE "C" BRACKET IS USED TO SUPPORT THE FIBERRUNNER 12x4 CABLE ROUTING SYSTEM FROM A SECTION OF NEW 1/2" (M12) THREADED ROD (NOT INCLUDED) OR CAN BE DIRECTLY MOUNTED TO THE CEILING.
- THE FIBERRUNNER 12x4 QUIKLOCK ADJUSTABLE "C" BRACKET INCLUDES:
 ONE (1) BRACKET ASSEMBLY,
 TWO (2) 1/2-13 HEAVY HEX NUTS (FR12ACB12 ONLY),
 TWO (2) M12x1.75 HEX NUTS (FR12ACB12M ONLY),
 TWO (2) 1/2 HELICAL SPRING LOCKWASHERS,
 ONE (1) 1/4-20 T-BOLT,
 ONE (1) 1/4-20 HEX KEPS LOCK NUT
- FINISH COLOR: BLACK (EXCEPT HARDWARE)
- DIMENSIONS IN PARENTHESES ARE IN METRIC.

ENG. REF.: D37797ER_DC_FR12ACB12_01.prt

CAD FILENAME/LAYERS

B FR12ACB12.pdf

PANDUIT CORP TINLEY PARK, ILLINOIS
 FIBERRUNNER 12x4 QUIKLOCK
 ADJUSTABLE "C" BRACKET - 1/2" (M12)
C THREADED ROD (FR12ACB12, FR12ACB12M)
 CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
 DIMENSIONAL TOLERANCES ARE:
 (.X) ± (.XXX) ±
 (.XX) ± .03 (.8) ANGLES ±

UNLESS OTHERWISE SPECIFIED,
 ALL DIMENSIONS ARE GIVEN IN
 INCHES, THIRD ANGLE PROJECTION.

DRAWN BY: JHNU
 DATE: 5-24-01
 CHK'D: HIW

MAT'L:

STEEL

SCALE: NONE

DRAWING NO.: 37797-100

DWG SIZE: A

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	GMBH
-	-----	---	--	E. REVISED GENERAL NOTES.	-----	--	--		
-	-----	---	--	D. REVISED PART WEIGHT. C. REVISED DRAWING TITLE.	-----	--	--		
1	1-3-07	MSO	RN	B. REVISED CAD FILENAME. A. REVISED AND REDRAWN.	37797-100	RN	RN		