

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

SUPPLIED LABELS

19	20	21	22	23	24
13	14	15	16	17	18
7	8	9	10	11	12
1	2	3	4	5	6

43	44	45	46	47	48
37	38	39	40	41	42
31	32	33	34	35	36
25	26	27	28	29	30

PANDUIT P/N



WEIGHT

CPPL48M6BLY

11.38 LB/10 PCS
(5161.9 g/10 PCS)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
4. PART INCLUDES:
 - 1- STAMPING
 - 8- 6 POSITION FACEPLATE WITH LABEL SLOT
 - 8- LABEL COVER
 - 8- LABEL
 - 1- SCREW KIT (INCLUDES FOUR #12-24 SCREWS)
 - 1- SCREW KIT (INCLUDES FOUR M6 SCREWS)
5. LABELS ARE PRE-NUMBERED (1-48) WITH BLANK SIDE FOR CUSTOM LABELING.



MODEL FILENAME		M01158AA_CPPL48M6BL_00.PRT		SIZE A
DRAWING FILENAME		M02479CD_DC_00A.PRT		
MINI-COM MODULAR 48 PORT M6 FACEPLATE PATCH PANEL WITH LABEL CUSTOMER DRAWING				
PANDUIT TM CORP. TINLEY PARK, ILL 60477		I.T. NUMBER N/A		
THIRD ANGLE PROJECTION		PRODUCT SPEC N/A		
DRAWN BY JsP		WORK INSTRUCTION N/A		
DATE 4-19-06		SCALE NONE		
CHK'D MJO		PART NO. CPPL48M6BLY		
MATERIAL: PANEL - CRS FACEPLATE - ABS		DRAWING NO. 02479-057		

NETWORK SYSTEMS

MAY 26 2006

ENGINEERING DEPT

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
R	4-19-06	JsP	MJO	RELEASED TO PRODUCTION	02479-057				