

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

1. FIBER OPTICAM TERMINATION KIT CONSISTS OF THE COMPONENTS LISTED IN TABLE.
2. SEE CURRENT CATALOG FOR ADDITIONAL INFORMATION PERTAINING TO THESE PRODUCTS.


FCAMKIT - FIBER OPTICAM TERMINATION KIT

PANDUIT PART NUMBER	DESCRIPTION	QTY	PANDUIT PART NUMBER	DESCRIPTION	QTY
CST115	FIBER CABLE JACKET STRIPPER	1	OCTTY	OPTICAM TERMINATION TOOL	1
FALCBTL	ALCOHOL BOTTLE (EMPTY)	1	FVFLPC-2.5SMY	PATCH CORD FOR OPTICAM 2.5 FERRULE CONNECTORS	1
FBFSP	FIBER BUFFER STRIPPER (NO NIK)	1	FVFLPC-1.25SMY	PATCH CORD FOR OPTICAM 1.25 FERRULE CONNECTORS	1
FSCDVR	SCREWDRIVER	1	N/A	STRIPPING TEMPLATES	1
FGLASS	SAFETY GLASSES	1	N/A	INSTALLATION INSTRUCTIONS	1
FTWEEZR	TWEEZERS	1	FWP-C	LINT-FREE WIPES	100
FWTRBTL	WATER BOTTLE	1	FSWB-C	CLEANING SWABS	100
FKS	ARAMID YARN SHEARS	1	FSTY	FIBER SAFETY TAB STICKERS	1
FWRKMAT	FIBER SAFE WORKMAT	1	PFX-0	FINE-TIP MARKING PEN	1
FJQCVR	FIBER CLEAVER TOOL	1	FKITCASE	FIBER OPTIC KIT UNIVERSAL CARRYING CASE	1

FIBER OPTICAM TERMINATION KIT
CUSTOMER DRAWING



PANDUIT™
CORP.
TINLEY PARK, ILL 60477



ALL DIMENSIONS ARE GIVEN IN INCHES
UNLESS OTHERWISE SPECIFIED.
DIMENSIONAL TOLERANCES ARE:
(.X) (.XXX) ± .010 (0.3)
(.XX) ± .03 (0.8) ANGLES

DRAWING FILENAME
MO2421AH_DC_00A.prt

SCALE
NONE

DRAWN BY
MC

REVIEW DRAWING NUMBERS

PART NO.
FCAMKIT

DATE
08-28-06

DRAWING NO.
02421-17

CHK'D

SIZE
A

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
R	09-01-06	MC		RELEASED TO PRODUCTION	02421-17				