


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

1. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AND TO INDICATE PACKAGE QUANTITY.
2. 110 CONNECTOR ON ONE END AND AN RJ45 MODULAR PLUG WIRED TO EIA/TIA 568B ON THE OTHER END. THE PATCH CORDS CAN BE USED WITH PAN-PUNCH 110 CONNECTING BLOCKS.
3. 110 CONNECTOR FEATURES INCLUDE A CLEAR CAP TO ENSURE PROPER CONNECTOR ORIENTATION. RETAINING CLIPS SECURE THE JACKET CLOSE TO THE POINT OF TERMINATION WHICH MINIMIZES WIRE UNTWISTING. INTEGRAL STRAIN RELIEF MINIMIZES STRESS ON WIRES DURING DISCONNECTION.
4. POLARIZED TO PREVENT REVERSE INSTALLATION TO CONNECTOR BLOCK.
5. DIMENSIONS IN PARENTHESES ARE IN METRIC.



H F

G

E

C

PANDUIT PART NUMBER	MIN. CABLE LENGTH	WEIGHT
P110PC41G2BY	2 FT.	.71 LB/10 PCS (322 g/10 PCS)
P110PC41G4BY	4 FT.	1.17 LB/10 PCS (531 g/10 PCS)
P110PC41G5BY	5 FT.	1.4 LB/10 PCS (635 g/10 PCS)
P110PC41G6BY	6 FT.	1.63 LB/10 PCS (740 g/10 PCS)
P110PC41G7BY	7 FT.	1.86 LB/10 PCS (844 g/10 PCS)
P110PC41G8BY	8 FT.	2.09 LB/10 PCS (948 g/10 PCS)
P110PC41G9BY	9 FT.	2.32 LB/10 PCS (1053 g/10 PCS)
P110PC41G12BY	12 FT.	3.01 LB/10 PCS (1366 g/10 PCS)
P110PC41G15BY	15 FT.	3.7 LB/10 PCS (1679 g/10 PCS)
P110PC41G1MBY	1 M	.998 LB/10 PCS (452 g/10 PCS)
P110PC41G2MBY	2 M	1.74 LB/10 PCS (792 g/10 PCS)
P110PC41G3MBY	3 M	2.49 LB/10 PCS (1131 g/10 PCS)
P110PC41G5MBY	5 M	3.98 LB/10 PCS (1810 g/10 PCS)

D

MODEL FILENAME	SIZE
DRAWING FILENAME	A
D35536BK_DC09_RJ45_01D	
PAN-PUNCH 110 PATCH CORD ASSEMBLIES CUSTOMER DRAWING	
PANDUIT TM CORP. TINLEY PARK, ILL 60477	
I.I. NUMBER	
PRODUCT SPEC	
WORK INSTRUCTION	
SCALE	
NONE	
PART NO.	
DRAWING NO.	
35536-09	

ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED.
DIMENSIONAL TOLERANCES ARE:
(.X) ± (.XXX) ±
(.XX) ± ANGLES ±

THIRD ANGLE PROJECTION
DRAWN BY
TPC
DATE
10-02-96
CHK'D
CEF

REVIEW DRAWING NUMBERS

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
4	7-18-07	BJN	EJH	I. PAN-PUNCH 110 PATCH CORD ASSEMBLIES WAS CATEGORY 5 110 TO RJ-45 EIA/TIA 568B PATCHCORD H. ADDED "Y" TO ALL P/N'S G. REMVD P/N'S P110PC41G13B AND P110PC41G8B	35536-09	EJH	REGA		
3	6-24-03	LZ	EJH	F. IN PART NO.'S JACKET IS GRAY E. REMOVED JACKET COLOR CHART. D. UPDATED DWG TO CURRENT STANDARDS.	35536-09	EJH			
2	4-27-99	TA	ELN	C. ADDED P/N'S P110PC4**1MB, P110PC4**2MB, P110PC4**3MB, P110PC4**5MB	35536-09	CVM			
1	6-11-98	JsP	CEF	B. UPDATED MODEL TO SHOW PROPER FORM. A. REMOVED ASSEMBLY PORTION OF NOTE #3.	35536-09	CEF			
R	10-02-96	TPC	CEF	RELEASED TO PRODUCTION	35536-09	CEF			