THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



FIGURE 1
DP5e 48 PORT PATCH PANEL

PANDUIT P/N	WEIGHT (APPROX.)
DPKR485E88TG	2.40 LB (1088.6 g)

NOTES:
1. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AS WELL AS OPTIONAL ICONS.
2. KIT INCLUDES THE FOLLOWING:
   1 - LABEL SET 1-24
   1 - LABEL SET 25-48
   1 - BLANK LABEL
   9 - LABEL HOLDERS
   1 - STRAIN RELIEF BAR
   1 - DP5e 48 PORT PATCH PANEL
   8 - 12-24 X 1/2" ROUND HEAD SCREWS
   4 - M6x1 X 15mm METRIC SCREWS
3. MATERIAL:
   PANEL HOUSING: STEEL
   RJ45 MODULE: THERMOPLASTIC RESIN UL94V-0
   PUNCHDOWN BLOCKS: THERMOPLASTIC RESIN UL94V-0
   BEZEL ASSEMBLY: THERMOPLASTIC RESIN UL94H-B
   RETENTION CAP: THERMOPLASTIC RESIN UL94V-0
   STRAIN RELIEF BAR: STEEL BAR STOCK
   LABEL: VINYL
   LABEL HOLDER: CLEAR VINYL
4. 48 PORT PATCH PANEL 8 POSITION 8 WIRE.
5. THE PATCH PANEL AND STRAIN RELIEF BAR ARE DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS.
6. DIMENSIONS IN PARENTHESES ARE IN METRIC.
7. USE 110 STYLE TERMINATION TOOL FOR PUNCHDOWN.
8. RETENTION CAPS (ONE PER CONNECTOR) PROVIDED FOR SNAP-IN ON TERMINATED CONNECTORS.

REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH
R	11/26/07	BJN	RJDU	RELEASE TO PRODUCTION	01537-52	VMB		

SIZE A

DRAWING FILENAME: M01537EM_DC52_00A.PRT

DP5E 48 PORT PATCH PANEL
WITH STRAIN RELIEF BAR AND LABEL KIT
CUSTOMER DRAWING

PANDUIT™ CORP.
TINLEY PARK, ILL 60477

THIRD ANGLE PROJECTION

ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED.
DIMENSIONAL TOLERANCES ARE:
(.X) ±.03 (.XXX) ±.005
(.XX) ±.01 ANGLES ± 1°

DRAWN BY: BJN
DATE: 11/26/07
CHK'D: RJDU
MAT'L:
REVIEW DRAWING NUMBERS:

I.I. NUMBER:
PRODUCT SPEC/ PKG SPEC:
ASSY METHOD/ TEST METHOD:
SCALE: NONE
PART NO.: SEE CHART
DRAWING NO.: 01537-52
SHEET 1 OF 2

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

FIGURE 2
LABEL KIT



FIGURE 3
STRAIN RELIEF BAR

MODEL FILENAME	SIZE A
DRAWING FILENAME: M01537EM_DC52_00A.PRT	
DP5E 48 PORT PATCH PANEL WITH STRAIN RELIEF BAR AND LABEL KIT CUSTOMER DRAWING	
PANDUIT™ CORP. TINLEY PARK, ILL 60477	I.I. NUMBER
	PRODUCT SPEC/ PKG SPEC
THIRD ANGLE PROJECTION	ASSY METHOD/ TEST METHOD
ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ±.03 (.XXX) ±.005 (.XX) ±.01 ANGLES ± 1°	SCALE: NONE
DRAWN BY: BJN	REVIEW DRAWING NUMBERS
	PART NO.: SEE CHART
DATE: 11/26/07	MAT'L
CHK'D: RJDU	DRAWING NO.: 01537-52 SHEET 2 OF 2

REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH
R	11/26/07	BJN	RJDU	SEE SHT.1 FOR REVISION HISTORY	01537-52	VMB		