

Security Wall-Mount and Accessories

Security DVR and 19-in. Rack Equipment Cabinet, Type 1



Industry Standards

UL 508A Listed; Type 1

CSA; Type 1
 NEMA/EEMAC; Type 1
 IEC 60529 IP20
 EIA 310-D (19-in. spacing for rack equipment)
 Hoffman is an ISO 9001 company

Application

These cabinets provide physical protection and access control to DVR, 19-in. equipment or other equipment. Mount the cabinet vertically or horizontally on any surface.

Features

- Houses 19-in. or shelf-mount equipment
- Top cover has tool-less removal, is captivated by door and secured by keylock, providing easy access and installation
- Solid top cover protects equipment from falling debris
- Two standard models are 4 and 6 RU high
- Radius corners give streamlined appearance and eliminate sharp edges
- Solid front door has 180-degree opening continuous hinge
- Quarter-turn keylock with two keys on door (code 333)
- Vented sides dissipate heat from equipment
- A fan-ready cutout is provided on left side

- 14 gauge steel rack angles are adjustable within the cabinet body
- Rack angle mounting square holes (.375 x .375 in.) with EIA universal hole spacing (1/4 x 5/8 x 5/8 x 1/4-in.)
- Knockouts on bottom and side for data and power cables
- Rubber feet provide secure placement and prevent scratches
- Fasteners and cage nuts included

Specifications

- Doors and body made of 18 gauge steel; top cover is 16 gauge steel
- Welded steel construction
- One set of rack angles included per EIA standard
- Included installation instructions show optional accessories

Finish

Pretreated steel coated with RAL 9005 black, light-textured, low-gloss polyester powder paint

Accessories

See also *Accessories*.
 Rack- and Panel-Mount Power Distribution Unit (PDU)
 Replacement Keys
 Dual Thermostat
 VELCRO® Cable Wrap
 VELCRO is a trademark of Velcro Industries B.V.

Bulletin: D85, DACCY, DWS1

Standard Product

| Catalog Number | AxBxC in./mm | Rack Units (RU) |
|----------------|----------------------------------|-----------------|
| DVR4U | 9.45x21.65x18.35 240x550x466 | 4 |
| DVR6U | 12.99x21.65x18.35 330x550x466 | 6 |

General Accessories

| Catalog Number | Description | Key Code |
|----------------|-------------------------------------|----------|
| E333KEY | 2 replacement keys (fits all locks) | 333 |
| A4AXFNGQ | Fan, 115 VAC, plus | |

Security Wall-Mount and Accessories

