





Note:

24 x RJ45 Port Patch Panel is 1RU (Rack Unit) in height.

48 x RJ45 Port Patch Panel is 2RU (Rack Unit) in height.

25-Pair RJ21 Male Connector




Available *PANDUIT* Patch Cords with 25-Pair RJ21 Male Connectors:

UTPCH*SR25Y
UTPCH*SL25Y
UTPCH*R25Y
UTPCH*LR25Y
UTPCH*L25Y

Replace * with patch cord length in feet (6, 8, 10, 15, or 20)


Securing 25-Pair Male RJ21 Connector with Hold-down Bracket




WIRING CHART

RJ21 POSITIONS	COLOR CODE REFERENCE	RJ45 PLUG POSITION	PAIRS	PORT
27	WHITE	1	PAIR 1	PORT 1, 7, 13, 19, 25, 31, 37, 43
2	ORANGE	2		
28	WHITE	3	PAIR 2	
3	GREEN	6		
26	WHITE	5	PAIR 3	
1	BLUE	4		
29	WHITE	7	PAIR 4	
4	BROWN	8		
31	RED	1	PAIR 5	PORT 2, 8, 14, 20, 26, 32, 38, 44
6	ORANGE	2		
32	RED	3	PAIR 6	
7	GREEN	6		
30	RED	5	PAIR 7	
5	BLUE	4		
33	RED	7	PAIR 8	
8	BROWN	8		
35	SLATE	1	PAIR 9	PORT 3, 9, 15, 21, 27, 33, 39, 45
10	ORANGE	2		
36	SLATE	3	PAIR 10	
11	GREEN	6		
34	SLATE	5	PAIR 11	
9	BLUE	4		
37	SLATE	7	PAIR 12	
12	BROWN	8		
39	BLACK	1	PAIR 13	PORT 4, 10, 16, 22, 28, 34, 40, 46
14	ORANGE	2		
40	BLACK	3	PAIR 14	
15	GREEN	6		
38	BLACK	5	PAIR 15	
13	BLUE	4		
41	BLACK	7	PAIR 16	
16	BROWN	8		
43	YELLOW	1	PAIR 17	PORT 5, 11, 17, 23, 29, 35, 41, 47
18	ORANGE	2		
44	YELLOW	3	PAIR 18	
19	GREEN	6		
42	YELLOW	5	PAIR 19	
17	BLUE	4		
45	YELLOW	7	PAIR 20	
20	BROWN	8		
47	VIOLET	1	PAIR 21	PORT 6, 12, 18, 24, 30, 36, 42, 48
22	ORANGE	2		
48	VIOLET	3	PAIR 22	
23	GREEN	6		
46	VIOLET	5	PAIR 23	
21	BLUE	4		
49	VIOLET	7	PAIR 24	
24	BROWN	8		
50	VIOLET	NONE	PAIR 25	
25	SLATE			

Panel RJ21 (Rear of Panel)



Panel RJ45 (Front of Panel)



For Instructions in Local Languages
and Technical Support:

www.panduit.com/resources/install_maintain.asp



www.panduit.com

E-mail:
cs@panduit.com

Fax:
(708) 444-6993