




⚠ MATERIAL:
CONNECTOR ASSY
REAR BODY: ALUMINUM ALLOY
PLUNGER: ALUMINUM ALLOY
FERRULE: STAINLESS STEEL
COUPLING NUT: ZINC, NICKEL PLATED
INTERNAL COMPONENTS: RUBBER, COLOR: BLACK
SPRING: STAINLESS STEEL
FRONT PROTECTIVE COVER: LDPE, COLOR: BLACK, NON-FR
CRIMP EYELET: COPPER, NICKEL PLATED
POLYMER TUBING: TYGON, COLOR: CLEAR
HYTREL, COLOR: WHITE
PVC, COLOR: BLACK
STRAIN RELIEF: POLYOLEFIN ELASTOMER, COLOR: BLACK, NON-FR
BOOT: POLYOLEFIN ELASTOMER, COLOR: BLACK*
*UL94 V-0 RATED AT QUALIFYING THICKNESS.

2. INSTRUCTION SHEET: 408-9860 AVAILABLE FOR DOWNLOAD AT
www.tycoelectronics.com/documents OR
www.ampnetconnect.com/foguide.
3. THIS KIT WILL TERMINATE:
900um TIGHT BUFFERED FIBER
250um COATED FIBER
2.0-3.0mm JACKETED CABLE

LOC		DIST		REVISIONS					
CE		00		P	LTR	DESCRIPTION	DATE	DWN	APVD
			A			RELEASE TO ACTIVE	08JUN2006	BB	LS
			AI			ADD NOTE 2	12MAR2009	BB	SB

125um	250um/0.8-1.0mm	5504034-1
FIBER SIZE	BUFFER SIZE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN B. BRIGGS 20JUN2005	Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: mm		CHK L. SAUERWEIN 20JUN2005		
		APVD S. BUCHTER 20JUN2005	NAME CONNECTOR KIT, XTC, STAINLESS STEEL, 2.5mm BAYONET, MULTIMODE	
		PRODUCT SPEC -	SIZE A200779	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC -	CAGE CODE C-5504034	
MATERIAL -		WEIGHT -	DRAWING NO -	
FINISH -		CUSTOMER DRAWING	SCALE 4:1	SHEET 1 OF 1
			REV A1	