

REV	MCO	DWN	DATE
E	20252817	LS	04-NOV-08
F	20271692	JM	26-AUG-09

NOTES:

1.0 SCOPE

THIS SPECIFICATION DEFINES THE REQUIREMENTS FOR A WALL PLATE MODULAR 4 PORT ASSY VARIOUS COLORS

2.0 APPLICABLE DOCUMENTS

2.1 UL 94 "TESTS FOR FLAMMABILITY OF PLASTIC MATERIALS"

2.2 ORDER OF PRECEDENCE

IN CASE OF CONFLICT, THE FOLLOWING ORDER OF PRECEDENCE SHALL APPLY:

- A. PURCHASE ORDER
- B. THIS DOCUMENT

3.0 REQUIREMENTS

3.1 MATERIALS

- 3.1.1 MATERIAL: ABS POLYLAC PA-765A OR EQUIVALENT.
- 3.1.2 COLOR: SEE TAB

3.2 DIMENSIONAL

- 3.2.1 SEE DRAWING
- 3.2.2 PART TO BE FREE OF BURRS, SCRATCHES, SPOTS AND NOTICEABLE SINK.

3.3 FLAMMABILITY:

- 3.3.1 FLAMMABILITY RATING: MATERIAL USED SHALL BE UL94 V-0 LISTED.

3.4 MARKING & MOLDING:

- 3.4.1 CLASSIFIED U.S. UL LOGO, CLASSIFIED CANADA UL LOGO, UP ARROW DIRECTION, CATALOG NUMBER AND ADC LOGO, SHOULD BE MOLDED INSIDE THE FACE PLATE.

4.0 QUALITY ASSURANCE PROVISIONS:

4.1 MANUFACTURING INSPECTION:

THE MANUFACTURER SHALL PREFORM AUDITS TO ENSURE 100% FUNCTIONALITY OF ALL RECEIVED PARTS. ADDITIONAL TESTING AND INSPECTIONS SHALL BE PREFORMED AS NEEDED TO ENSURE THAT ALL REQUIREMENTS ARE MET.

4.2 QUALITY CONFORMANCE INSPECTION

BUYER RESERVES THE RIGHT TO RETURN AT THE MANUFACTURER'S EXPENSE ANY NONCONFORMING MATERIALS OR LOTS WHICH DO NOT MEET SAMPLING INSPECTION REQUIREMENTS.

4.3 DESIGN AND PROCESS CHANGE:

NO CHANGES IN MATERIAL DESIGN OR PROCESS WHICH WILL AFFECT FORM, FIT OR FUNCTION SHALL BE MADE BY THE MANUFACTURER AFTER SAMPLE APPROVAL WITHOUT WRITTEN AUTHORITY FROM THE BUYER. THE TERM "FUNCTIONAL" IMPLIES SECTION 3.0 PARAMETERS.


5.0 PACKAGING AND HANDLING REQUIREMENTS:

5.1 MAXIMUM CONTAINER WEIGHT: 40 LBS.


5.2 SHIPPING CONTAINER MARKING(S)

SHIPPING CONTAINERS SHALL BE MARKED WITH THE FOLLOWING AS A MINIMUM:

- 1. MANUFACTURER'S NAME AND/OR LOGO
- 2. ADC PART NUMBER
- 3. ADC PURCHASE ORDER NUMBER
- 4. QUANTITY ENCLOSED
- 5. (PREFERRED BUT OPTIONAL INFORMATION):
NUMBER OF SEPARATE PACKAGES/BOXES
("BOX# ---- OF ---- BOXES")



F/N 005 DETAIL



ADC P/N	CATALOG	REV	COMPONENT F/N 001 (DESCRIPTION) QTY 1	COMPONENT F/N 002 INST SHT 4 PORT WALL PLATE (COLOR) QTY 1	COMPONENT F/N 003 (DESCRIPTION) QTY 1	COMPONENT F/N 004 WALL PLATE, MODULAR 4 PORT (COLOR) QTY 1	PANTONE COLOR	FEDERAL STANDAR SPECIFICATION	COMPONENT F/N 005 POLYBAG ID TABS & DESIGNATION (COLOR) QTY 1
6644115401	6644 1 154-01	B	PA111 0212 00 00 POLYBAG CLEAR 4X7 IN. .002 THICK	1436364	POLYBAG W/(2) #6-32X15/16 COMBO SCREWS	6644 3 154-01 (WHITE)	---	FED STD. 37925	6630 3 114-01 (WHITE)
6644115402	6644 1 154-02	B				6644 3 154-02 (IVORY)	---	FED STD. 27886	6630 3 114-02 (IVORY)
6644115403	6644 1 154-03	B				6644 3 154-03 (GRAY)	421C	FED STD. 25630	6630 3 114-03 (GRAY)
6644115404	6644 1 154-04	B				6644 3 154-04 (BLACK)	6C2X	FED STD 27038	6630 3 114-04 (BLACK)
6644115405	6644 1 154-05	A				6644 3 154-05 (RED)	187C	FED STD 11350	6630 3 114-05 (RED)
6644115422	6644 1 154-22	B				6644 3 154-22 (ELECTRICAL IVORY)	4545U	---	6630 3 114-22 (ELECTRICAL IVORY)
1458405	6644 1 154-24	A				6644 3 154-24 (ELECTRICAL BROWN)	440C	---	6630 3 114-24 (ELECTRICAL BROWN)

NOTES:

1. ALL POLYBAG IT SHOULD BE SEALED AT BOTH ENDS.



INFORMATION ON THIS DOCUMENT IS PROPRIETARY TO ADC AND SHALL NOT BE USED, COPIED, REPRODUCED OR DISCLOSED IN WHOLE OR IN PART WITHOUT WRITTEN CONSENT OF ADC.

ALL DIMS AND TOLERANCES ARE INCHES UNLESS OTHERWISE SPECIFIED

DO NOT SCALE DRAWING

TITLE
ASSY WALL PLATE
MODULAR 4 PORT

DRAWING NUMBER
66441154XX

ENGR: LUIS SANCHEZ
DWN: JUAN MONCADA

SHT. 1 OF 1

DIMENSIONS IN INCHES
THIRD ANGLE PROJECTION