



## General Accessories

### 19-in. and 23-in. Rack Angles



Made of 14 gauge steel with square holes or 12 gauge steel with 10-32 tapped holes. Provides 19- or 23-in. rack spacing depending on frame width. Finished with flat black RAL 9005 polyester powder paint or plated. Furnished in pairs.

Bulletin: DNCY, DWDH1



| Catalog Number | Rack Spacing | Hole Type | Finish | Use With                  | Fits Frame Height | Fits Frame Width | Rack Units | L (mm) | L (in.) |
|----------------|--------------|-----------|--------|---------------------------|-------------------|------------------|------------|--------|---------|
| ERA197THLN     | 19 in.       | Square    | Black  | Networking Cabinet - SOHO | 700mm             | 600mm            | 11         | 492    | 19.38   |
| ERA197TPLN     | 19 in.       | Tapped    | Black  | Networking Cabinet - SOHO | 700mm             | 600mm            | 11         | 492    | 19.38   |
| ERA1921TPL     | 19 in.       | Tapped    | Black  | Seismic Cabinet           | 2100mm            | 700mm            | 45         | 2003   | 78.87   |
| ERA192321TPL   | 19 & 23 in.  | Tapped    | Black  | Seismic Cabinet           | 2100mm            | 800mm            | 45         | 2003   | 78.87   |
| ERA1910TPL     | 19 in.       | Tapped    | Black  | Network PC Cabinet        | Bottom Section    | —                | 19         | 848    | 33.37   |
| ERA1924TPLWM   | 19 in.       | Tapped    | Plated | Wall Mount Cabinet        | 24 in.            | —                | 12         | 533    | 21.00   |
| ERA1960TPLWM   | 19 in.       | Tapped    | Plated | Wall Mount Cabinet        | 60 in.            | —                | 32         | 1422   | 55.98   |

### Rack Unit Label




Self-adhesive clear Mylar™ label with white numbers enables numbering along sides of open frame racks or rack angles. Numbers spaced one rack unit apart. Can be used for bottom-up or top-down numbering of rack units to simplify equipment installation. Each label provided in two pieces (numbers 1-29 and 30-58) for easier installation. Two labels per catalog number. Label shown mounted on rack angle.

Mylar is a registered trademark of DuPont Tejin Films.

Bulletin: DOFRY

| Catalog Number | Installed Length in./mm | Width in./mm |
|----------------|-------------------------|--------------|
| ARULABEL       | 101.50<br>2578          | .50<br>13    |


### Tool-less (Snap-in) Blanking Panels for 19-in. Racks



These Tool-less 19-in. Blanking Panels provide easy tool-less installation and ensure proper airflow to equipment. Made of black composite material and can be used with tapped or square EIA universal spaced rack mounting angles.

Bulletin: DACCY

| Catalog Number | Description            | Rack Units | Fits   | Pkg. Qty. |
|----------------|------------------------|------------|--|-----------|
| D19BPT1RU      | Blanking Panel, 19 in. | 1          | 19 in., universal rack spacing, tapped or square holes | 10        |
| D19BPT2RU      | Blanking Panel, 19 in. | 2          | 19 in., universal rack spacing, tapped or square holes | 10        |



General Accessories


Rack Panel for 19-in. Racks



Used to cover unused rack space in cabinets or open frame racks for a finished appearance. Can also be used for surface mounting small devices. Panels are flat with mounting slots spaced at 19-in. EIA standard spacing. Made of 12 gauge steel with RAL 9005 black polyester powder paint finish. Mounting hardware sold separately.

Bulletin: DOFRY

| Catalog Number | Rack Units | E (in.) | E (mm) |
|----------------|------------|---------|--------|
| P19RPP1UB      | 1          | 1.75    | 44     |
| P19RPP2UB      | 2          | 3.50    | 89     |
| P19RPP3UB      | 3          | 5.25    | 133    |
| P19RPP4UB      | 4          | 7.00    | 178    |
| P19RPP5UB      | 5          | 8.75    | 222    |
| P19RPP6UB      | 6          | 10.50   | 267    |



Touch-Up Paint



For repairing the finish of any painted parts.

Bulletin: DACCY, P20

| Catalog Number | Description    |
|----------------|----------------|
| ATPG7035       | RAL 7035 Gray  |
| ATPB9005       | RAL 9005 Black |