

## New features

- Flash memory microprocessor
- Expanded event log
- Early open/late close reporting
- Programmable loop response

## Standard features

- Full data reporting
- Expandable to 8 fully programmable hardwire and/or wireless zones
- Maximum of 8 keypads
- 8 user codes
- 512-event history log that provides date, time, event and user number
- Wireless technology with up to 8 supervised zones
- Hardwire expansion up to 8 zones
- Supports SIA and contact ID communication formats
- CP-01 Compliant

## Overview

The NetworX NX-4 is a feature-rich, entry level security system. The NX-4 uses advanced technology for burglary, fire and environmental detection without the high cost of similar controls. The NX-4 is a flexible security system that is both easy to install and simple to use. With up to eight zones, the NX-4 is ideal for apartment, small residential and small commercial applications.

## Outstanding features

The NX-4 panel comes standard with four hardwire zone inputs. Four programmable outputs can be set up to activate external devices during an alarm or other system event. The modular design allows for complete integration of multiple systems within one enclosure. Adding more zones or expanding capability is fast and easy.

## Convenient and flexible

Conduct quick and easy on-site programming with alphanumeric keypads and a menu driven text interface. Off-site programming is also available with the DL-900 software for Windows.

# NetworX Control Panel NX-4



## NetworX Control Panel NX-4

### Specifications

- Operating Power – 16.5V AC 40VA
- Auxiliary w/40VA or 50VA transformer – 1 Amp
- Auxiliary w/NX-320E power supply – 3 Amps\*

### Loop resistance

- For standard loop – 300 $\Omega$  Maximum
- Built-in siren driver – 2 Tone (Steady & Yelp)
- Alarm current available (if driver is not used)
  - 2.5 Amps

### Operating temperature

- 32 to 120°F

### Dimensions

- 6.40 inches wide
- 4.0 inches high
- 1.10 inches deep

### Shipping weight

- 8 pounds

\* When using the NX-320E (w/50VA transformer) rated at 2 Amps and NX-4 (w/40VA or 50VA transformer) rated at 1 Amp, the combined available power is 3 Amps.

12345 SW Leveton Drive  
Tualatin, OR 97062  
Phone: 503-692-4052  
USA & Canada: 800-547-2556  
Technical Service: 800-727-2339  
Faxback: 800-483-2495

1275 Red Fox Road  
Arden Hills, MN 55112  
Phone: 651-777-2690  
USA & Canada: 800-777-5484  
Technical Service: 800-777-2624

[www.gesecurity.com](http://www.gesecurity.com)

## Available Keypad Styles



LED



LCD with  
Removable Door



Fixed Display with  
Removable Door



LED with  
Removable Door

NetworX Technical Support: 800-727-2339