

MR4050 Mount

CEILING/WALL MOUNT, MONITOR

Product Features

- Ceiling or Wall Mounting
- Accommodates Monitors 19 to 31 Inches (49 to 79 cm) Wide
- Supports up to 150 Pounds (68 kg)
- Tilt Angle Adjustable in Increments of ± 20 Degrees and ± 40 Degrees
- Replaces MR4000 Monitor Mount; Features Include Safety Straps and Fully Braced Monitor Support Pan

The **MR4050** monitor mount is designed to mount a monitor safely from either a ceiling or a wall. It can be used in security systems, educational institutions, churches, hospitals, and other applications requiring overhead monitor mounting and positioning.


The **MR4050** will accept monitors from 19 to 31 inches (49 to 79 cm) wide and features safety straps and a fully braced monitor support pan. The safety straps wrap around the sides and back of the monitor to seat and stabilize the monitor in the support pan, thus minimizing monitor movement. The tilt angle for the monitor support pan is adjustable in increments of ± 20 degrees and ± 40 degrees. Cosmetic covers conceal locking bolts in the side arm brackets.

The **MR4050** will safely support monitors weighing up to 150 pounds (68 kg).

An 8-inch (20.32 cm) section of 1.5-inch NPT threaded pipe is furnished with the mount to allow for either ceiling or wall mounting. Two optional adapters are available: the MRCA for ceiling mounting and the MRWA for wall mounting.



(SAFETY STRAPS NOT SHOWN)



NOTE: VALUES IN PARENTHESES ARE CENTIMETERS;
ALL OTHERS ARE INCHES.



TECHNICAL SPECIFICATIONS

MODEL

MR4050	Universal monitor mount; fits monitors from 19 to 31 inches (49 to 79 cm) wide
--------	--

RELATED PRODUCTS

MRCA	Ceiling mount adapter (uses four 5/16-inch diameter fasteners, not supplied).
MRWA	Wall mount adapter (uses a minimum of six 5/16-inch diameter fasteners, not supplied).

Note: The mounting surface must be able to support the total weight of the monitor and the mount.

GENERAL

Tilt Angle	Adjustable increments of $\pm 20^\circ$ or $\pm 40^\circ$
Maximum Load	150 lb (68 kg)
Construction	Steel
Finish	Black polyester powder coat
Environment	Indoor only
Unit Weight	
MR4050	27.40 lb (12.43 kg)
MRCA	1.22 lb (0.55 kg)
MRWA	11.35 lb (5.15 kg)
Shipping Weight	
MR4050	31 lb (14.06 kg)
MRCA	2 lb (0.9 kg)
MRWA	13 lb (5.88 kg)



Pelco, Inc. Worldwide Headquarters:
3500 Pelco Way, Clovis, California 93612-5699 USA
USA & Canada Tel: (800) 289-9100 • FAX: (800) 289-9150
International Tel: +1 (559) 292-1981 • FAX: +1 (559) 348-1120
www.pelco.com

Pelco and the Pelco logo are registered trademarks of Pelco, Inc.
Product specifications and availability subject to change without notice.
©Copyright 2000, Pelco, Inc. All rights reserved.