

Lightest DECT™ headset  
on the market

Enjoy best-in-class PC audio



## Wireless freedom that won't weigh you down **Savi® 440**

The highest level of wearing style choice and best-in-class PC audio in one convenient, portable package.

**plantronics®**

# Savi 440

**Wireless freedom that won't weigh you down.** The first portable DECT headset system now includes the lightest headset on the market—the Savi 440. Experience best-in-class PC sound quality with a versatile headset that can be worn three ways to match your personal style. A hot swappable battery\* for unlimited talk time and up to 300 feet of wireless freedom make this headset a productivity powerhouse.

## SUPERIOR CALL MANAGEMENT

- Manage PC voice communications and multi-media with the lightest DECT wireless headset on the market
- Hot swappable battery\* lets you change battery mid-conversation delivering unlimited talk time
- One-touch call answer/end/flash, vol+/-, mute from the headset for simple PC call management
- An energy-efficient adaptive power system, delivers longer talk and standby times

## OUTSTANDING AUDIO QUALITY

- DECT technology provides better audio; eliminates interference from Wi-Fi networks
- Advanced wideband audio using CAT-iq technology for high definition voice quality
- Noise-canceling microphone reduces background noise interruptions, ensuring great audio quality and easing listener fatigue
- Enhanced Digital Signal Processing (DSP) provides more natural sounding voice

## RECOMMENDED ACCESSORIES

- Deluxe charging cradle kit, charges headset and spare battery (includes cradle + battery)
- Deluxe USB charging kit, charges headset and spare battery (includes charger + battery)




## GLOBAL CUSTOMER CARE

Backed by Plantronics industry leading global service and support.

800-544-4660 (US and Canada)  
831-458-7700 (outside US)

For more information about the Savi 440 or other Plantronics products, please visit our website at [plantronics.com](http://plantronics.com)



## OPTIMIZED FOR UNIFIED COMMUNICATIONS

|                    |                                                                                                                                                                                                                          |
|--------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Connects to        | PC via USB adapter                                                                                                                                                                                                       |
| Ideal for          | Users in campus-like business environments using a laptop for voice calls and requiring the highest sound quality and portability                                                                                        |
| Talk time          | Up to 7 hrs*                                                                                                                                                                                                             |
| Headset weight     | 21 grams                                                                                                                                                                                                                 |
| Wireless frequency | DECT 6.0, range up to 300 ft.                                                                                                                                                                                            |
| Audio performance  | PC Wideband: up to 6,800 Hz                                                                                                                                                                                              |
| Hearing protection | Soundguard® DIGITAL™: protects against sound levels above 118dBA; Anti-startle detects and eliminates any large sudden increase in signal level; Time-Weighted Average prevents average noise level from exceeding 85dBA |
| Limited warranty   | 1 year                                                                                                                                                                                                                   |
| Models             | W440: UC Standard version built for UC applications and softphones from Avaya®, Cisco®, IBM®, Skype® and more<br><br>W440-M: Version optimized for Microsoft® Lync™ 2010 and Microsoft OCS 2007                          |

\*Unlimited talk time with hot swappable battery (additional battery sold separately)

©2011 Plantronics, Inc. All rights reserved. Plantronics, the Sound World graphic, Savi, and SoundGuard are trademarks or registered trademarks of Plantronics, Inc. Microsoft and Lync are trademarks or registered trademarks of Microsoft Corporation in the U.S. and other countries. IBM is a trademark of International Business Machines Corporation, registered in many jurisdictions worldwide. DECT is a trademark of ETSI. All other trademarks are the property of their respective owners. 05/11

