



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: B013-330

KVM Switch Accessories- Cat5e KVM Console Extender Kit

Highlights

- Manage a PS/2 or USB computer/KVM switch from a remote location up to 330ft (100m) away
- Use readily available Cat5e cable for interconnection



Description

Tripp Lite's B013-330 Cat5e KVM Extender Kit utilizes Cat5 cabling to extend your computer's Keyboard, Monitor, and Mouse control up to 100 meters (330 ft.) away. The Cat5 KVM Extender Set comprises two units - the Transmitter (Local Unit) and the Receiver (Remote Unit). The Transmitter Unit contains local console ports, allowing the user to have both a local and remote console. The Receiver Unit contains Gain and Equalization knobs that allow the user to manually adjust the video parameters of the remote console. Users can easily optimize the video screen output via these mechanical knobs.

Package Includes






- Transmitter and Receiver Unit (1 each)
- 3-ft. PC/KVM Cable Kit (1)
- Power Adapter (DC9V, 1A) for Receiver Unit (1)
- 4-ft. USB A-B Cable (1)
- Quick Start Guide

Features

- Enables you to control a PS/2 or USB computer/KVM switch from a distance of up to 330ft (100m) away.
- Can control the computer or KVM switch via both Local and Remote Consoles.
- The remote connection is made using standard Cat5e cable
- Display mode of 1600 x 1200 @ 60Hz
- Shielded Cat5e cables provide better transmission integrity

Specifications

| OVERVIEW | |
|-----------------------|--------------------------------|
| Model Type | Console Extender Kits |
| PRODUCT OVERVIEW | |
| Product Overview | Cat5e KVM Console Extender Kit |
| PHYSICAL | |
| Shipping weight (lbs) | 2.04 |

| | |
|---|---|
| Shipping Dimensions (HWD/in) | 6.9 x 8 x 5.5 |
| Color | Silver |
| Transmitter Unit Height Inches | 1 |
| Transmitter Unit Width Inches | 5.2 |
| Transmitter Unit Depth Inches | 2.6 |
| Receiver Unit Height Inches | 1 |
| Receiver Unit Width Inches | 5.2 |
| Receiver Unit Depth Inches | 2.6 |
| CONNECTIONS | |
| Other Ports |  (x2) RJ45 (Female) |
| Included KVM Cable (Equipment Side) - Connector 1 |  HD15 (Male) |
| Included KVM Cable (Equipment Side) - Connector 2 | (x2) MiniDIN6 (Male) |
| Included KVM Cable (Equipment Side) - Connector 3 |  USB A (Male) |
| Local Console Ports - Port 1 |  HD15 (Female) |
| Local Console Ports - Port 2 | (x2) MiniDIN6 (Female) |
| Remote Console Ports - Port 1 |  HD15 (Female) |
| Remote Console Ports - Port 2 | (x2) MiniDIN6 (Female) |
| WARRANTY | |
| Product Warranty Period (Worldwide) | 1-year limited warranty |

Related Items

Optional Products

| Related Model | Description | Qty. |
|-----------------------------|--|------|
| N105-025-GY | 25-ft. Cat5e 350MHz Molded Shielded Patch Cable (RJ45 M/M) - Gray | 1 |
| N105-050-GY | 50-ft. Cat5e 350MHz Molded Shielded Patch Cable (RJ45 M/M) - Gray | 1 |
| N105-100-GY | 100-ft. Cat5e 350MHz Molded Shielded Patch Cable (RJ45 M/M) - Gray | 1 |

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=3883.

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.