



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: B021-000-19

### Rackmount Console - 1U Rackmount Console with 19" LCD



#### Highlights

- Control an entire network in just 1U of rack space; includes keyboard, 19" LCD screen and touch pad
- Connects to a PS/2 or USB server or KVM switch
- Supports resolutions up to 1280 x 1024
- Rackmountable in 19" system rack (1U), from 27" to 42" deep

#### Description

Tripp Lite's B021-000-19 1U Rackmount Console features an integrated 19" LCD display, full 88-key keyboard and touch pad, all in a 1U rackmountable housing. The included KVM cable kit allows for connection to a PS/2 computer or KVM, and a PS/2 to USB adapter is included, which can be used to connect to a USB computer or KVM. Constructed of heavy-duty steel housing.

#### Applications

- Use where rack space is at a premium, and where a Server/KVM display is needed

#### System Requirements

- Computer or KVM with a VGA monitor port and USB or PS/2 keyboard/mouse ports

#### Package Includes


- 1U Rackmount Console w/ 19" LCD
- 1- KVM Cable Kit ( HD15M to HD15M + 2 PS2 Male )
- 1-PS/2 to USB Adapter
- 1- C13 to 5-15P Power Cord
- 1- User Manual
- Mounting Hardware

#### Features

- Features 19-inch LCD TFT active-matrix, color panel
- Space saving 1U 19-inch, rackmount drawer design
- Supports resolutions of up to 1280 x 1024
- Included PS/2 to USB adapter allows for connection to a USB computer or KVM
- Sleep mode when the monitor cover is closed
- Input 120/240 VAC
- Constructed of heavy-duty steel housing

#### Specifications

OVERVIEW	
PC/Server	VGA, USB or PS/2

<b>PHYSICAL</b>	
Color	Black
Style	1U Rack Console (non-KVM)
<b>CONNECTIONS</b>	
Connector A	 HD15 (FEMALE)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

## Related Items

### Optional Products

Related Model	Description	Qty.
<a href="#">WEXT3-KVM-CONS</a>	3-Year Extended Warranty - For B021-000-19 Rackmount Console	1
<a href="#">WEXT5-KVM-CONS</a>	5-Year Extended Warranty - For B021-000-19 Rackmount Console	1
<a href="#">B064-032-04-IPG</a>	KVM Switch - 32-Port (4-User) 1U Rackmount Cat5 Matrix KVM Switch	1
<a href="#">B060-016-2</a>	KVM Switch - 16-Port (2-User) 1U Rackmount Cat5 Matrix KVM Switch	1
<a href="#">B004-008</a>	KVM Switch - 8-Port 1U Rackmount KVM Switch	1
<a href="#">B019-000</a>	KVM Switch Accessories - 2-Post Rackmount Bracket for B020,B021, B040, and B070 Consoles and KVM Consoles	1
<a href="#">B072-016-1</a>	KVM Switch - 16-Port NetCommander 1U Rackmount Cat5 KVM Switch	1
<a href="#">B022-U16</a>	KVM Switch - 16-Port NetDirector 1U Rackmount KVM Switch	1
<a href="#">B072-008-1</a>	KVM Switch - 8-Port NetCommander 1U Rackmount Cat5 KVM Switch	1
<a href="#">B007-008</a>	KVM Switch - 8-Port 1U Rackmount KVM Switch with On-Screen Display	1
<a href="#">B021-000-17</a>	Rackmount Console - 1U Rackmount Console with 17" LCD	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.triplite.com/en/products/model.cfm?txtModelID=3691](http://www.triplite.com/en/products/model.cfm?txtModelID=3691).

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.