



ZC12A3B24LP-F010

InstaPATCH® ZERO Cord Cassette with twelve Category 6A U/UTP patch cords, dark gray jacket, tail length 10 feet, 24 OM4 Fiber Ruggedized Fanout

Configuration Specifications

ANSI/TIA Category	6A
Cable Types	Mixed media
Fiber Type	LazrSPEED® 550, 50 µm multimode fiber
Jacket Color, copper	Dark gray
Jacket Color, fiber	Aqua
Fiber Construction Type	Ruggedized fanout
Interface Feature, copper connector A	Standard
Interface Feature, copper connector B	Standard
Interface, copper connector A	RJ45 plug
Interface, copper connector B	RJ45 plug
Interface, fiber connector A	LC
Interface, fiber connector B	MPO Male
Port Quantity, copper	12
Port Quantity, fiber	12

Dimensions

Tail Length	3.0 m 10.0 ft
Connection Range, overhead	914.4 mm 36.0 in
Depth	711.2 mm 28.0 in
Height	289.6 mm 11.4 in
Weight	9.07 kg 20.00 lb
Width	43.7 mm 1.7 in

Environmental Specifications

Safety Standard	CE cETL ETL
-----------------	-----------------

General Specifications

Brand	InstaPATCH® ZERO SYSTIMAX®
Color	Black
Finish	Powder-coated, smooth
Ordering Note	Available in Mexico, Central America, and South America Available in the United States and Canada
Package, quantity	1

Mechanical Specifications

Material Type	Plastic Steel
---------------	-----------------

ZC12A3B24LP-F010

Regulatory Compliance/Certifications

Agency

RoHS 2002/95/EC

ISO 9001:2008

Classification

Compliant

Designed, manufactured and/or distributed under this quality management system



Included Products

860474246 | 1095B DG 4/24 RVAR (Product Component—not orderable) — GigaSPEED® X10D 1095B Category 6A U/UTP Cable, non-plenum, dark gray jacket, 4 pair count, variable length, reel

FLXMXLCAF — LazrSPEED® 550 MPO (male) to LC, InstaPATCH® 360 Ruggedized Fanout Cable, 24-Fiber, Plenum

- P-024-MP-5K-F12 (Product Component—not orderable) — Plenum MPO Trunk Cable, 24 fiber with 12 fiber subunits
- 860366228 (Product Component—not orderable) — LazrSPEED® Low Loss MPO Male 12 Fiber Connector, aqua
- 460125198 (Product Component—not orderable) — Pre-Radiused LC Connector duplex for 1.6 mm Fiber, multimode