



ZC12B2B24LP-F008

InstaPATCH® ZERO Cord Cassette with twelve Category 6 U/UTP patch cords, light blue jacket, tail length 8 feet, 24 OM4 Fiber Ruggedized Fanout

Configuration Specifications

ANSI/TIA Category	6
Cable Types	Mixed media
Fiber Type	LazrSPEED® 550, 50 µm multimode fiber
Jacket Color, copper	Light blue
Jacket Color, fiber	Aqua
Fiber Construction Type	Ruggedized fanout
Interface Feature, copper connector A	Standard
Interface Feature, copper connector B	Standard
Interface, copper connector A	RJ45 plug
Interface, copper connector B	RJ45 plug
Interface, fiber connector A	LC
Interface, fiber connector B	MPO Male
Port Quantity, copper	12
Port Quantity, fiber	12

Dimensions

Tail Length	2.4 m 8.0 ft
Connection Range, overhead	914.4 mm 36.0 in
Depth	711.2 mm 28.0 in
Height	289.6 mm 11.4 in
Weight	8.16 kg 18.00 lb
Width	43.7 mm 1.7 in

Environmental Specifications

Safety Standard	CE cETL ETL
-----------------	-----------------

General Specifications

Brand	InstaPATCH® ZERO SYSTIMAX®
Color	Black
Finish	Powder-coated, smooth
Ordering Note	Available in Mexico, Central America, and South America Available in the United States and Canada
Package, quantity	1

Mechanical Specifications

Material Type	Plastic Steel
---------------	-----------------

ZC12B2B24LP-F008

Regulatory Compliance/Certifications

Agency

RoHS 2002/95/EC
ISO 9001:2008

Classification

Compliant
Designed, manufactured and/or distributed under this quality management system



Included Products

860017037 | 1074E LB 4/24 RVAR (Product Component—not orderable) — GigaSPEED® XL 1074E Category 6 U/UTP Cable, non-plenum, light blue jacket, 4 pair count, variable length, reel

FLXMXLCAF — LazrSPEED® 550 MPO (male) to LC, InstaPATCH® 360 Ruggedized Fanout Cable, 24-Fiber, Plenum

- P-024-MP-5K-F12 (Product Component—not orderable) — Plenum MPO Trunk Cable, 24 fiber with 12 fiber subunits
- 860366228 (Product Component—not orderable) — LazrSPEED® Low Loss MPO Male 12 Fiber Connector, aqua
- 460125198 (Product Component—not orderable) — Pre-Radiused LC Connector duplex for 1.6 mm Fiber, multimode