



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: P774-006

6-ft. KVM Switch PS/2 (3-in-1) Cable Kit for B020-008/016 series B022-016 and B022 desktop series

Highlights

- Connects a PS/2 Computer to Tripp Lite's NetDirector KVM Switches (B020- and B022-Series KVM Switches)
- Makes management and organization of cables much easier
- KVM Switch side of the cable kit consists of a HD15 Male cable
- Computer side of the cable kit consists of a HD15 Male cable, a PS/2 (MiniDIN6) Male Mouse cable and a PS/2 (MiniDIN6) Male Keyboard cable
- Molded, color-coded connectors



Description

Tripp Lite's 6-ft. PS/2 (3-in-1) KVM cable kit is designed to connect a PS/2 computer or a console converter to Tripp Lite's NetDirector KVM switches (all B020 and B022 Series KVM Switches). This premium 3-in-1 cable provides superior performance and cable management. It consists of two PS/2 keyboard/mouse cables and a monitor cable bonded into a single unit. This low profile cable is incredibly flexible making cable management a breeze. All cables are manufactured from superior molded cable with integral strain relief and foil shielding for maximum EMI/RFI protection.

System Requirements

- A PS/2 computer or an adapter (model # B015-000) for a non-PS/2 computer.
- A Tripp Lite B020 or B022 Series KVM Switch.

Package Includes



- 6-ft. PS/2 Cable Kit for Tripp Lite's NetDirector KVM Switches (B020- and B022-Series KVM Switches)

Features

- Connects a PS/2 computer to Tripp Lite's NetDirector KVM switches (B020- and B022-Series KVM Switches)
- KVM Switch side of the cable kit consists of a HD15 Male cable
- Computer side of the cable kit consists of a HD15 Male cable, a PS/2 (MiniDIN6) Male Mouse cable and a PS/2 (MiniDIN6) Male Keyboard cable
- Provides superior performance and cable management
- Molded ends with easy-grip textured overmold
- Low profile cable is super flexible and easy to control
- Superior molded cable with integral strain relief and double shielding (foil and braid) for maximum EMI/RFI protection

Specifications

OVERVIEW	
Model Type	Cable Kits
INPUT	

Cable Length (ft.)	6
Cable Length (m)	1.83
CONNECTIONS	
Connector A	 HD15 (MALE)
Connector B	 (X2) MINI DIN-6 (MALE)
CERTIFICATIONS	
Certifications	RoHS-Compliant
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

Related Items

Optional Products

Related Model	Description	Qty.
B013-330	KVM Switch Accessories - KVM Console Extender Kit	1
B015-000	USB Adapters - USB to PS/2 Adapter	1
B020-016-17	Console KVM Switch - 16-Port NetDirector 1U Rackmount Console KVM Switch w/17" LCD	1
B022-U16	KVM Switch - 16-Port NetDirector 1U Rackmount KVM Switch	1
P774-010	10-ft. KVM Switch PS/2 (3-in-1) Cable Kit for B020-008/016 series B022-016 and B022 desktop series	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=2579.

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.