

Accessories


Mechanical

T1 - T7

Tmax
MCCBs



KT3100-3



KT1HTC-3



KT4LTC-3

Standard cable terminal

Frame	Wire Size	Catalog number (set of 2)	List Price	Catalog number (set of 3)	List Price	Catalog number (set of 4)	List Price
T1	14AWG-1/0	—	—	Integral	—	Integral	—
T2	14AWG-1/0	—	—	KT2100-3	\$ 9	KT2100-4	\$ 12
T3	14AWG - 1/0	—	—	KT3100-3	9	KT3100-4	12
	4AWG - 300kcmil	—	—	KT3225-3	18	KT3225-4	24
Ts3	14AWG-2AWG	KTS3060-2	\$ 19	KTS3060-3	27	KTS3060-4	36
	14AWG-1/0	KTS3100-2	19	KTS3100-3	27	KTS3100-4	36
	2AWG-4/0	KTS3150-2	26	KTS3150-3	36	KTS3150-4	54
	4AWG-300kcmil	KTS3225-2	26	KTS3225-3	36	KTS3225-4	72
T4	14AWG-1/0	KT4100-2	18	KT4100-3	9	KT4100-4	12
	6AWG-350kcmil	KT4250-2	60	KT4250-3	30	KT4250-4	40
T5	250kcmil-500kcmil	KT5300-2	90	KT5300-3	45	KT5300-4	60
T5 ①	(2) 3/0-250kcmil	KT5400-2	90	KT5400-3	45	KT5400-4	60
T5 ②	(2) 3/0-500kcmil	—	—	KT5600-3	225	—	—
T6	(2) 250-500kcmil	—	—	KT6600-3	270	KT6600-4	360
T6 ①	(3) 2/0-400kcmil	—	—	KT6800-3	350	KT6800-4	470
T7 ①	(4) 4/0-500kcmil	—	—	KT7X1200-3	560	KT7X1200-4	747

Standard cable lug kits with power control taps

Frame	Wire Size	Catalog number (set of 2)	List Price	Catalog number (set of 3)	List Price	Catalog number (set of 4)	List Price
T3	14AWG - 1/0	—	—	KT3100-3C	\$ 16	KT3100-4C	\$ 19
	4AWG - 300kcmil	—	—	KT3225-3C	18	KT3225-4C	31
Ts3	14AWG-1/0	KTS3100-2C	\$ 34	KTS3100-3C	48	KTS3100-4C	57
	2AWG-4/0	KTS3150-2C	34	KTS3150-3C	48	KTS3150-4C	57
	4AWG-300kcmil	KTS3225-2C	53	KTS3225-3C	75	KTS3225-4C	93
T4	14AWG-1/0	KT4100-2C	30	KT4100-3C	15	KT4100-4C	15
	6AWG-350kcmil	KT4250-2C	72	KT4250-3C	36	KT4250-4C	48
T5	250kcmil-500kcmil	KT5300-2C	102	KT5300-3C	51	KT5300-4C	68
T5 ①	(2) 3/0-250kcmil	KT5400-2C	102	KT5400-3C	51	KT5400-4C	68
T6	(2) 250-500 kcmil	—	—	KT6600-3C	310	KT6600-4C	414
T6 ②	(3) 2/0-400kcmil	—	—	KT6800-3C	403	KT6800-4C	541

Terminal covers for fixed breakers - Low profile-kit includes two pieces

Frame	Catalog number (3 pole)	List Price	Catalog number (4 pole)	List Price
T1	KT1LTC-3	\$ 35	KT1LTC-4	\$ 47
T2	KT2LTC-3	40	KT2LTC-4	54
T3	KT3LTC-3	50	KT3LTC-4	68
Ts3	KTS3LTC-3	50	KTS3LTC-4	68
T4	KT4LTC-3	55	KT4LTC-4	74
T5	KT5LTC-3	60	KT5LTC-4	81
T6	KT6LTC-3	66	KT6LTC-4	88
T7 ③	KT7LTC-3	70	KT7LTC-4	93

Terminal covers for fixed breakers - High profile-kit includes two pieces

Frame	Catalog number (3 pole)	List Price	Catalog number (4 pole)	List price
T1	KT1HTC-3	\$ 37	KT1HTC-4	\$ 50
T2	KT2HTC-3	43	KT2HTC-4	58
T3	KT3HTC-3	53	KT3HTC-4	72
Ts3	KTS3HTC-3	53	KTS3HTC-4	72
T4	KT4HTC-3	58	KT4HTC-4	78
T5	KT5HTC-3	63	KT5HTC-4	85
T6	KT6HTC-3	66	KT6HTC-4	88
T7	KT7XHTC-3	77	KT7XHTC-4	104

① Comes standard with high profile terminal covers.
 ② Uses front extended spreaded terminals-refer to technical catalog.
 ③ Fixed breaker only.

Accessories T1...T3 Mechanical

Acc.




KT3RH



OHB65J6




OHY65J6




KT3LD



KT3100-3



KT2EF-3



KT2R-3

Direct mount rotary operator handle

	Catalog number	List price
Direct mount rotary	KT3RH	

Early make contact

Frame	Catalog number	List price
T2-T3	KT3EM	

Allows the UVR or control to be supplied in advance. Mounted inside the direct rotary handle.

Variable depth rotary handles

Frame	Mechanism catalog number	List price	Shaft catalog number	List price	Handle catalog number	List price
NEMA 1, 3R, 12						
Tmax	KT3VD-M		OXp6X430 ①		OHY65J6 ① OHB65J6 ①	
NEMA 4, 4X						
Tmax	KT3VD-M		OXp6X430 ①		OHY80L6 ① OHB80L6 ①	
NEMA 1						
Tmax	KT3VD-M		KT3VD-S		KT3VD-H	

Locking device

	Catalog number	List price
Locking device, open/closed	KT3LD	
Locking device, open	KT3LDO	

Lugs

For breakers	Amps	Wire size	Set of 2 catalog number	List price	Set of 3 catalog number	List price	Set of 4 catalog number	List price
Standard cable lugs								
T2	100	14AWG-1/0	KT2100-2		KT2100-3		KT2100-4	
T3	60 225	14AWG-2AWG 4AWG-350kcmil	KT3060-2 KT2250-2		KT3060-3 KT3225-3		KT3060-4 KT3225-4	

Extended front terminals

For breakers	Amps	Set of 3		Set of 4	
		Catalog number	List price adder	Catalog number	List price
T2	100	KT2EF-3		KT2EF-4	
T3	225	KT3EF-3		KT3EF-4	

Rear terminals

For breakers	Amps	Set of 3		Set of 4	
		Catalog number	List price adder	Catalog number	List price
T2	100	KT2R-3		KT2R-4	
T3	225	KT3R-3		KT3R-4	

OHB 65 J 6

Color
B = Black
Y = Red/Yellow

Physical size (length in mm)

Shaft size (diameter in mm)

J = Type 1, 3R, 12
L = Type 1, 3R, 12, 4, 4X

① Use Discount schedule DS-H.

Discount schedule DS-STA
Discount schedule DS-H — Handles