



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: B078-101-PS2

KVM Switch Accessories - NetCommander PS2 Server Interface Module

Highlights

- Needed to connect a PS/2 Server to a B070 / B072-Series NetCommander KVM switch via Cat5e cable
- Easy to install; no software needed
- No power supply needed
- Allows a recommended maximum distance of 100ft from KVM to Server via Cat5e cable
- Compact and lightweight design



Description

Tripp Lite's NetCommander PS/2 Server Interface Module connects to the HD15 port and PS/2 ports on a computer/server, and converts them to a single RJ45 connector. Ordinary Cat5e patch cables can then be used to connect the computer/server to the switch ports on a Tripp Lite B070 / B072-Series NetCommander Cat5 KVM switch. Use of Cat5e cables frees up space in the installation that would be filled by traditional, thicker KVM cables.

System Requirements

- Server or CPU with a HD15 port and (2) PS/2 type connections
- A B070 / B072-Series NetCommander Cat5 KVM Switch
- Cat5e/6 cable; up to 100ft

Package Includes

- 1 PS/2 Server Interface Module

Features

- Eliminates the need for thicker, heavier KVM cables
- Compact, lightweight design
- Plug and Play; no software required
- No power supply required
- Allows a Server/CPU to be located up to 100ft away from the KVM switch

Specifications

OVERVIEW	
Application	Connects a PS/2 computer/server to a B070 / B072-Series NetCommander Cat5 KVM Switch
Model Type	Interface Modules
CONNECTIONS	

Connector A	 RJ45 (FEMALE)
Connector B	 HD15 (MALE)
Side B - Connector 2	(x2) MiniDIN6 (Male)
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

Related Items

Required Products

Related Model	Description	Qty.
B070-016-19-IP	NetCommander 19" Console w/ 16-Port Cat5 IP KVM Switch	1
B070-016-19	NetCommander 19" VGA Console Cat5 KVM Switch - 16 Port	1
B070-008-19	NetCommander 19" VGA Console Cat5 KVM Switch - 8 Port	1
B072-016-1-IP	KVM Switches- 16-Port NetCommander 1U Rackmount Cat5 KVM Switch w/IP	1
B072-016-1	KVM Switch - 16-Port NetCommander 1U Rackmount Cat5 KVM Switch	1
B072-008-1	KVM Switch - 8-Port NetCommander 1U Rackmount Cat5 KVM Switch	1

Optional Products

Related Model	Description	Qty.
B078-101-USB	KVM Switch Accessories - NetCommander USB Server Interface Module	1
N201-010-GY	10-ft. Cat6 Gigabit Snagless Molded Patch Cable (RJ45 M/M) - Gray	1
N201-014-GY	14-ft. Cat6 Gigabit Snagless Molded Patch Cable (RJ45 M/M) - Gray	1
N201-025-GY	25-ft. Cat6 Gigabit Snagless Molded Patch Cable (RJ45 M/M) - Gray	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=4330.

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.