



CompuLink fiber optic patch cord

LC (ceramic) to LC (ceramic) 2-fiber aqua jacketed 50/125 OM2 riser rated zipcord.

* Built using Corning connectors and cordage.

* Individually bagged.

ANIXTER PART No.	VENDOR PART No.	LENGTH FT.	LENGTH MT.
243793	LCCLCC50D1	3.3 FT.	1 MT.
246794	LCCLCC50D2	6.6 FT.	2 MT.
246795	LCCLCC50D3	10.0 FT.	3 MT.
275058	LCCLCC50D4	13.1 FT.	4 MT.
246796	LCCLCC50D5	16.4 FT.	5 MT.
275059	LCCLCC50D6	19.7 FT.	6 MT.
305121	LCCLCC50D7	23.0 FT.	7 MT.
275060	LCCLCC50D8	26.2 FT.	8 MT.
246797	LCCLCC50D10	32.8 FT.	10 MT.
275061	LCCLCC50D12	39.4 FT.	12 MT.
275062	LCCLCC50D15	49.2 FT.	15 MT.
275064	LCCLCC50D18	59.1 FT.	18 MT.
348779	LCCLCC50D20	65.6 FT.	20 MT.

NOTICE: THIS COMPULINK DRAWING IS BEING PROVIDED FOR PURPOSES OF PROPOSAL AND DESIGN DISCUSSION ONLY. COMPULINK RECOGNIZES THAT THE CUSTOMER MAINTAINS DESIGN AUTHORITY OVER THE SUBJECT PRODUCT AND AS SUCH, THE CUSTOMER MAINTAINS FULL RESPONSIBILITY FOR DESIGN EVALUATION, APPROVAL, AND QUALIFICATION. COMPULINK DRAWINGS ARE PROVIDED FOR REFERENCE ONLY AND ARE NOT TO BE USED FOR SPECIFICATION OR DESIGN CONTROL PURPOSES.

CONFIDENTIAL: THE CONTENTS OF THIS DRAWING ARE CONFIDENTIAL AND CONSTITUTE THE EXCLUSIVE PROPERTY OF COMPULINK CABLE ASSEMBLIES INC. THIS DRAWING'S CONTENTS MAY NOT BE MADE PUBLIC IN ANY MANNER, DISTRIBUTED OR LOANED TO OTHERS OR REPRODUCED OR COPIED EITHER IN WHOLE OR PART WITHOUT THE PRIOR WRITTEN CONSENT OF THE COMPANY.

REV	DESCRIPTION	DATE	BY

DRAWN: G.KRUG	DATE 2/27/12
CHECKED: DATE	
APPROVALS	DATE
ENGINEERING: DATE	
QUALITY: DATE	



CADD REF. No.:
LCLCOM2RISER

DRAWING NO.
LC-LC-OM2-RISER