



## CompuLink fiber optic patch cord

**LC (ceramic) to SC (ceramic) 2-fiber aqua jacketed 50/125 OM2 riser rated zipcord.**

\* Built using Corning connectors and cordage.

\* Individually bagged.

NOTICE: THIS COMPU LINK DRAWING IS BEING PROVIDED FOR PURPOSES OF PROPOSAL AND DESIGN DISCUSSION ONLY. COMPU LINK RECOGNIZES THAT THE CUSTOMER MAINTAINS DESIGN AUTHORITY OVER THE SUBJECT PRODUCT AND AS SUCH, THE CUSTOMER MAINTAINS FULL RESPONSIBILITY FOR DESIGN EVALUATION, APPROVAL, AND QUALIFICATION. COMPU LINK DRAWINGS ARE PROVIDED FOR REFERENCE ONLY AND ARE NOT TO BE USED FOR SPECIFICATION OR DESIGN CONTROL PURPOSES.

CONFIDENTIAL: THE CONTENTS OF THIS DRAWING ARE CONFIDENTIAL AND CONSTITUTE THE EXCLUSIVE PROPERTY OF COMPU LINK CABLE ASSEMBLIES INC. THIS DRAWING'S CONTENTS MAY NOT BE MADE PUBLIC IN ANY MANNER, DISTRIBUTED OR LOANED TO OTHERS OR REPRODUCED OR COPIED EITHER IN WHOLE OR PART WITHOUT THE PRIOR WRITTEN CONSENT OF THE COMPANY.

ANIXTER PART No.	VENDOR PART No.	LENGTH FT.	LENGTH MT.
246801	LCCSCC50D1	3.3 FT.	1 MT.
246802	LCCSCC50D2	6.6 FT.	2 MT.
246803	LCCSCC50D3	10.0 FT.	3 MT.
269234	LCCSCC50D4	13.1 FT.	4 MT.
246804	LCCSCC50D5	16.4 FT.	5 MT.
269235	LCCSCC50D6	19.7 FT.	6 MT.
328245	LCCSCC50D7	23.0 FT.	7 MT.
264449	LCCSCC50D8	26.2 FT.	8 MT.
246805	LCCSCC50D10	32.8 FT.	10 MT.
269236	LCCSCC50D11	36.1 FT.	11 MT.
275065	LCCSCC50D12	39.4 FT.	12 MT.
264450	LCCSCC50D15	49.2 FT.	15 MT.
275066	LCCSCC50D18	59.1 FT.	18 MT.

REV	DESCRIPTION	DATE	BY

DRAWN: G.KRUG	DATE 2/29/12
CHECKED: DATE	
APPROVALS	DATE
ENGINEERING:	
QUALITY:	



CADD REF. No.:  
LCSCOM2RISER

DRAWING NO.  
LC-SC-OM2-RISER