



Number of contacts

5



Identification	Part number	Drawing	Dimensions in mm
Han-Yellock® module	11 05 105 3001		

Identification	Wire gauge (mm²)	Part number	Drawing	Dimensions in mm																																				
Han-Yellock® crimp contacts Male contact Han-Yellock® TC20 silver plated 	0.14-0.37 0.5 0.75 1 1.5 2.5 3 4	11 05 000 6101 11 05 000 6102 11 05 000 6103 11 05 000 6104 11 05 000 6105 11 05 000 6106 11 05 000 6107 11 05 000 6108	 <table><tr><th colspan="3">Wire gauge</th><th>Stripping length</th></tr><tr><td>0.14-0.37</td><td>mm²</td><td>AWG 26-22</td><td>6.5 mm</td></tr><tr><td>0.5</td><td>mm²</td><td>AWG 20</td><td>6.5 mm</td></tr><tr><td>0.75</td><td>mm²</td><td>AWG 18</td><td>6.5 mm</td></tr><tr><td>1</td><td>mm²</td><td>AWG 18</td><td>6.5 mm</td></tr><tr><td>1.5</td><td>mm²</td><td>AWG 16</td><td>6.5 mm</td></tr><tr><td>2.5</td><td>mm²</td><td>AWG 14</td><td>6.5 mm</td></tr><tr><td>3</td><td>mm²</td><td>AWG 12</td><td>6.5 mm</td></tr><tr><td>4</td><td>mm²</td><td>AWG 12</td><td>6.5 mm</td></tr></table>	Wire gauge			Stripping length	0.14-0.37	mm²	AWG 26-22	6.5 mm	0.5	mm²	AWG 20	6.5 mm	0.75	mm²	AWG 18	6.5 mm	1	mm²	AWG 18	6.5 mm	1.5	mm²	AWG 16	6.5 mm	2.5	mm²	AWG 14	6.5 mm	3	mm²	AWG 12	6.5 mm	4	mm²	AWG 12	6.5 mm	
Wire gauge			Stripping length																																					
0.14-0.37	mm²	AWG 26-22	6.5 mm																																					
0.5	mm²	AWG 20	6.5 mm																																					
0.75	mm²	AWG 18	6.5 mm																																					
1	mm²	AWG 18	6.5 mm																																					
1.5	mm²	AWG 16	6.5 mm																																					
2.5	mm²	AWG 14	6.5 mm																																					
3	mm²	AWG 12	6.5 mm																																					
4	mm²	AWG 12	6.5 mm																																					
Removal tool for crimp contacts		09 99 000 0319																																						