



COLOR CODE
AS SHOWN

P-1		P-2	
1	WHT-ORG	1	
2	ORG-WHT	2	
3	WHT-GRN	3	
4	BLU-WHT	4	
5	WHT-BLU	5	
6	GRN-WHT	6	
7	WHT-BRN	7	
8	BRN-WHT	8	



Cat 6 Stranded UTP riser rated patch cord, without boots

RJ45 plug to RJ45 plug, 568B wiring

These cable assemblies are tested to the Category 6 component compliant requirements of TIA/EIA-568-B.2 for the following:

Frequency range 1 to 250 MHz

Wire map

Attenuation

NEXT

PSNEXT

ELFEXT

PSACR

Return loss

Propagation delay

Delay skew

ANIXTER PART NO.	VENDOR PART NO.	JACKET COLOR
MMXX-AXC6-01	M88DEXXFC601	WHITE
MMXX-AXC6-02	M88DEXXFC602	BLACK
MMXX-AXC6-03	M88DEXXFC603	RED
MMXX-AXC6-04	M88DEXXFC604	GREEN
MMXX-AXC6-05	M88DEXXFC605	YELLOW
MMXX-AXC6-06	M88DEXXFC606	BLUE
MMXX-AXC6-08	M88DEXXFC608	ORANGE
MMXX-AXC6-09	M88DEXXFC609	GRAY
MMXX-AXC6-10	M88DEXXFC610	VIOLET

NOTICE: THIS COMPULINK DRAWING IS BEING PROVIDED FOR PURPOSES OF PROPOSAL AND DESIGN DISCUSSION ONLY. COMPULINK RECOGNIZES THAT THE CUSTOMER MAINTAINS DESIGN AUTHORITY OVER THE SUBJECT PRODUCT AND AS SUCH, THE CUSTOMER MAINTAINS FULL RESPONSIBILITY FOR DESIGN EVALUATION, APPROVAL, AND QUALIFICATION. COMPULINK DRAWINGS ARE PROVIDED FOR REFERENCE ONLY AND ARE NOT TO BE USED FOR SPECIFICATION OR DESIGN CONTROL PURPOSES.

CONFIDENTIAL: THE CONTENTS OF THIS DRAWING ARE CONFIDENTIAL AND CONSTITUTE THE EXCLUSIVE PROPERTY OF COMPULINK CABLE ASSEMBLIES INC. THIS DRAWING'S CONTENTS MAY NOT BE MADE PUBLIC IN ANY MANNER, DISTRIBUTED OR LOANED TO OTHERS OR REPRODUCED OR COPIED EITHER IN WHOLE OR PART WITHOUT THE PRIOR WRITTEN CONSENT OF THE COMPANY.

DRAWN:	G.KRUG	DATE	2/3/12
CHECKED:		DATE	
APPROVALS		DATE	
ENGINEERING:			
QUALITY:			



CADD REF. No.:
CAT6NOBOOTPATCHCORD
DRAWING NO.
CAT6NOBOOTPATCHCORD

REV	DESCRIPTION	DATE	BY