




COLOR CODE
AS SHOWN

P-1		P-2
1	WHT-ORG	1
2	ORG-WHT	2
3	WHT-GRN	3
4	BLU-WHT	4
5	WHT-BLU	5
6	GRN-WHT	6
7	WHT-BRN	7
8	BRN-WHT	8



Cat 6 Stranded UTP riser rated patch cord, with slim line boots

RJ45 plug to RJ45 plug, 568B wiring

These cable assemblies are tested to the Category 6 component compliant requirements of TIA/EIA-568-B.2 for the following:

Frequency range 1 to 250 MHz

Wire map

Attenuation

NEXT

PSNEXT

ELFEXT

PSACR

Return loss

Propagation delay

Delay skew

NOTICE: THIS COMPULINK DRAWING IS BEING PROVIDED FOR PURPOSES OF PROPOSAL AND DESIGN DISCUSSION ONLY. COMPULINK RECOGNIZES THAT THE CUSTOMER MAINTAINS DESIGN AUTHORITY OVER THE SUBJECT PRODUCT AND AS SUCH, THE CUSTOMER MAINTAINS FULL RESPONSIBILITY FOR DESIGN EVALUATION, APPROVAL, AND QUALIFICATION. COMPULINK DRAWINGS ARE PROVIDED FOR REFERENCE ONLY AND ARE NOT TO BE USED FOR SPECIFICATION OR DESIGN CONTROL PURPOSES.

CONFIDENTIAL: THE CONTENTS OF THIS DRAWING ARE CONFIDENTIAL AND CONSTITUTE THE EXCLUSIVE PROPERTY OF COMPULINK CABLE ASSEMBLIES INC. THIS DRAWING'S CONTENTS MAY NOT BE MADE PUBLIC IN ANY MANNER, DISTRIBUTED OR LOANED TO OTHERS OR REPRODUCED OR COPIED EITHER IN WHOLE OR PART WITHOUT THE PRIOR WRITTEN CONSENT OF THE COMPANY.

ANIXTER PART NO.	VENDOR PART NO.	JACKET COLOR
MMXX-AXC6-01B	M88DEXXFC601B	WHITE
MMXX-AXC6-02B	M88DEXXFC602B	BLACK
MMXX-AXC6-03B	M88DEXXFC603B	RED
MMXX-AXC6-04B	M88DEXXFC604B	GREEN
MMXX-AXC6-05B	M88DEXXFC605B	YELLOW
MMXX-AXC6-06B	M88DEXXFC606B	BLUE
MMXX-AXC6-08B	M88DEXXFC608B	ORANGE
MMXX-AXC6-09B	M88DEXXFC609B	GRAY
MMXX-AXC6-10B	M88DEXXFC610B	VIOLET

REV	DESCRIPTION	DATE	BY

DRAWN: G.KRUG	DATE 2/3/12
CHECKED: DATE	
APPROVALS	DATE
ENGINEERING: DATE	
QUALITY: DATE	



CADD REF. No.:
CAT6BOOTEDPATCHCORD
DRAWING NO.
CAT6BOOTEDPATCHCORD