



Product information GSC 300 schwarz/black

Industrial Connecting Solutions:Rectangular Connectors:Valve Connectors (Type A -B -C):Type A:Receptacle Valve Connectors (DIN EN 175 301-803):GSC 300 schwarz/black

<http://www.e-catalog.beldensolutions.com/link/57078-24228-256261-256266-256270-276216-35142/en/conf/ui/istate>

Name GSC 300 schwarz/black



appliance connector with retaining nut, PE contact, 2 screws M 3 x 10 and 1 screw M 3 x 5, without contacts

Delivery informations

Availability available

Product description

Description appliance connector with retaining nut, PE contact, 2 screws M 3 x 10 and 1 screw M 3 x 5, without contacts

Type GSC 300 schwarz/black

Order No. 931 382-100

Number of contacts 2 + PE / 3 + PE

Standard DIN EN 175 301-803-A

Housing Color black

Construction type A

Technical data

Rated voltage AC/DC 400 V

Rated current 16 A

Contact resistance $\leq 4 \text{ m}\Omega$

Type of termination crimp (ground contacts: screw)

Mounting screw

Material

Contact surface material Sn

Contact bearer material PA

Housing material PA

Environmental conditions

Protection class (IEC 60529) IP 65 (gasket necessary) (mated)

Pollution severity 3

Temperature range -40 °C to +125 °C

Inflammability class

Contact bearer 94 HB

Approvals

VDE VDE

SEV SEV

Packing unit

Packaging unit 100 pieces

Scope of delivery and accessories

Accessories to order separately (NBR) flat gasket GSA 200-4, Order no. 730 843-002; (EPDM) flat gasket GSA 200-7, Order no. 730 268-003; Crimpkontakte RMC 480, Order no. 731 470-021; Crimpzange XZC 0702, Order no. 932 507-009



HIRSCHMANN


A BELDEN BRAND

Industrial Connecting Solutions:Rectangular Connectors:Valve Connectors (Type A -B -C):Type A:Receptacle Valve Connectors (DIN EN 175 301-803):GSC 300 schwarz/black

<http://www.e-catalog.beldensolutions.com/link/57078-24228-256261-256266-256270-276216-35142/en/conf/ui/state>

Picture

Drawing



Belden Deutschland GmbH

Im Gewerbepark 2

58579 Schalksmühle

Germany

Phone: +49 7127/14-1806

E-Mail: icos-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.