



Product information PC150/36V/48V-IP67

Industrial Ethernet: System Accessories: Power supply: PC150/36V/48V-IP67

<http://www.e-catalog.beldensolutions.com/link/57078-24455-24544-24545-64728/en/conf/ui/state>

Name	PC150/36V/48V-IP67
	
	DC/DC converter with 48 V power output
Delivery informations	
Availability	available
Product description	
Description	DC/DC converter with 48 V power output
Type	PC150/36V/48V-IP67
Order No.	943 968-001
More Interfaces	
Voltage input	1.1 m cable
Voltage output	0.5 m cable with M12-connector A-Coded
Power requirements	
Operating voltage	16.8 VDC to 64 VDC
Input data	
230 V	16.8 VDC to 64 VDC
Current consumption	
230 V	max. 8.929 A at 16.8 VDC max. 2.344 A at 64 VDC
Activation current	n/a
Output data	
Output voltage	48 V DC
Output current	
230 V	max. 3.125 A at 48 V DC
Service	
Diagnostics	n/a
Redundancy	
Redundancy functions	n/a
Ambient conditions	
Operating temperature	-40 °C to +70 °C
Storage/transport temperature	-55 °C to +85 °C
Relative humidity (non-condensing)	max. 100 % with condensing
MTBF	n/a
Mechanical construction	
Dimensions (W x H x D)	240 mm x 65 mm x 115 mm
Mounting	Wall mounting
Weight	3.1 kg
Protection class	IP 67
EMC interference immunity	
EN 50082-1	EN 61000-6-1
EN 50082-2	EN 61000-6-2
EMC emitted immunity	
EN 50081-1	61000-6-3, 61000-6-4, EN 55011, EN 55022 Klasse A
EN 50081-2	EN 61000-3-2
Approvals	
Safety of information technology equipment	cUL 60950-1 (pending)
Railway norm	EN 50121-4, EN50155

Industrial Ethernet: System Accessories: Power supply: PC150/36V/48V-IP67

<http://www.e-catalog.beldensolutions.com/link/57078-24455-24544-24545-64728/en/conf/ui/state>

Scope of delivery and accessories

Scope of delivery	DC/DC converter, installation guide and manual
--------------------------	--

For more information please contact:

Hirschmann Automation and Control GmbH

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: inet-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.