

## Fish Tape Accessories

### Poly Pull Line

- Use polypropylene line with manual or power fishing systems for light duty cable or rope pulling applications.
- Ready to use storage containers quickly dispense a tangle free line and also protects line from direct sunlight.
- Line is resistant to rot and mildew.
- Up to 210 lbs. average breaking strength.

Cat. No.	Description	Container Type	Weight (lbs.)
56108	500' (152 m) poly pull line w/ orange tracer	one-quart size w/locking lid	1
56110	6500' (1981 m) poly pull line with orange tracer	five-gallon bucket	11



56108



56110

### Steel Fish Tape Puller

- Exclusive design improves your grip while pulling all types of flat steel fish tape.
- Rugged metal construction is comfortable in your hand and provides excellent leverage.
- Internal resistance mechanism securely locks fish tape in place for pulling.
- Compatible with 1/8" & 1/4" tape widths and thicknesses of .045", .062" and .030".
- Compact size – fits easily in your pocket or a tool pouch.



50355

Cat. No.	Length	Weight (lbs.)
50355	3-1/4" (83 mm)	.33

### Composite Fish Tape Puller



56106

- Exclusive design improves your grip while pulling round-diameter, composite fish tapes.
- Flexible rubberized construction is comfortable in your hand and provides excellent leverage.
- Wide channel allows you to reposition the Fish Tape quickly and easily.
- Interlocking teeth molded into channel wrap completely around the tape when squeezed.
- Fits conveniently into center of 13" Fish Tape case for easy storage.
- Compatible with 3/16" Nylon, Fiberglass and Spiral Steel tapes.

Cat. No.	Length	Weight (lbs.)
56106	7 - 3/4" (196 mm)	.6

### Steel Fish Tape Swivel Eyelet

- For use with 1/8" wide steel fish tapes.
- Swivel head design helps prevent kinks and allows smoother, easier fishing in tight turns.
- High capacity eyelet holds up to five #12 unstripped wires or seven #10 bare wires.
- High strength steel construction allows for optimal performance over repeated uses.
- Retrofit instructions included.

Cat. No.	Length	Diameter	Weight (lbs.)
50351	1-1/2" (38 mm)	3/16" (5 mm)	.03



50351

All dimensions are in inches and (millimeters) unless otherwise specified.

**▲WARNING:** Wear approved eye protection when feeding, pulling or rewinding fish tape.

**▲WARNING:** Never remove screws while fish tape is coiled inside reel.

**▲WARNING:** Do NOT use any fish tape on or near live circuits. Use extreme caution when working near any electrical equipment.

**▲WARNING:** Use a safe work position to avoid loss of balance when using fish tape.