



## Product information GSA 2000 A schwarz/black

Industrial Connecting Solutions:Rectangular Connectors:Valve Connectors (Type A -B -C):Type A:Receptacle Valve Connectors (DIN EN 175 301-803):GSA 2000 A schwarz/black

<http://www.e-catalog.beldensolutions.com/link/57078-24228-256261-256266-256270-276216-35134/en/conf/ui/istate>

Name GSA 2000 A schwarz/black



appliance connector with retaining nut, without screws, longitudinal slots, closed nut

### Delivery informations

Availability available

### Product description

Description appliance connector with retaining nut, without screws, longitudinal slots, closed nut

Type GSA 2000 A schwarz/black

Order No. 932 592-500

Number of contacts 2 + PE

Standard DIN EN 175 301-803-A

Housing Color black

Construction type A

### Technical data

Rated voltage AC/DC 400 V

Rated current 16 A

Contact resistance  $\leq 4 \text{ m}\Omega$

Type of termination solder, holes for possibility of soldering on both sides (ground contacts: screw)

Mounting screw

### Material

Contact surface material Sn

Contact bearer material PA

Housing material PA

### Environmental conditions

Protection class (IEC 60529) IP 65 (gasket necessary) (mated)

Pollution severity 3

Temperature range  $-40 \text{ }^\circ\text{C}$  to  $+125 \text{ }^\circ\text{C}$

### Inflammability class

Contact bearer 94 V-0

### Approvals

UR UR

VDE VDE

SEV SEV

CSA CSA

### Packing unit

Packaging unit 200 pieces


### Scope of delivery and accessories

Accessories to order separately (NBR) flat gasket GSA 200-4, Order no. 730 843-002; (EPDM) flat gasket GSA 200-7, Order no. 730 268-003

Industrial Connecting Solutions:Rectangular Connectors:Valve Connectors (Type A -B -C):Type A:Receptacle Valve Connectors (DIN EN 175 301-803):GSA 2000 A schwarz/black  
<http://www.e-catalog.beldensolutions.com/link/57078-24228-256261-256266-256270-276216-35134/en/conf/ui/state>

Picture

Drawing



**Belden Deutschland GmbH**

Im Gewerbepark 2  
58579 Schalksmühle  
Germany  
Phone: +49 7127/14-1806  
E-Mail: [icos-sales@belden.com](mailto:icos-sales@belden.com)

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.