



With 1,500 feet of cable in each box, versus standard 1,000 ft boxes, *smartPAK* delivers the convenience and ease of use of a traditional pull-box with the additional benefits of 50% more cable.

All core UTP plenum and riser products are available in all colors
LANmark-1000 | LANmark-6 | LANmark-350 | Hyper Plus 5e

YOU ASKED FOR IT. WE LISTENED.

Introducing the 1500 ft innovation from Berk-Tek

Our innovative new box includes 1500 ft of cable so your installs are more efficient than ever.

**Save time. Save money.
Cut the scrap.**

FEATURES & BENEFITS

1500' box virtually eliminates cable scrap.

- When installing standards compliant 90 meter horizontal cable runs or even "typical" 45 meter runs.

More efficient installations.

- More cable pulls per box
- Fewer box change-over's
- Fewer boxes to breakdown or recycle
- Fewer boxes to handle or transport

Reduction in jobsite waste.

- 10%-15% reduction in cardboard per 1,000 ft

BOX DESIGN

Multi-layer corrugated box top for added strength with innovative thumb hole for better grip.

- Additional full flap box bottom resists carton sagging
- Double wall corrugated material improves stacking strength
- Box is approximately 2 cu. ft. in size – 18" L x 12" W x 16.5" H

"I never understood why a thousand feet of cable was the norm, especially when you consider that standards are in 300 foot increments. This new 1,500 foot box just makes sense for my jobs and my budget."
– Monty F., VP of Business Development



Learn more at berktek.com

smart PAK 1500ft

LANmark™ -1000

Category 6 UTP
CMP OD: 0.230"
CMR OD: 0.228"
Length per box: 1,500 ft.

Electrical Characteristics
Guaranteed to 350 MHz
Characterized to 550 MHz

Guaranteed Margin to Std.
NEXT 5 dB
PSNEXT 5 dB
ACR 5 dB
PSACR 5 dB
ACRF 5 dB
PSACRF 5 dB



PART NUMBER	FLAME RATING	COLOR
11074694	Plenum CMP	Blue
11074738	Plenum CMP	White
11074739	Plenum CMP	Gray
11074701	Riser CMR	Blue
11074740	Riser CMR	White
11074741	Riser CMR	Gray

LANmark™ -6

Category 6 UTP
CMP OD: 0.224"
CMR OD: 0.210"
Length per box: 1,500 ft.

Electrical Characteristics
Guaranteed to 250 MHz
Characterized to 500 MHz

Guaranteed Margin to Std.
NEXT 2 dB
PSNEXT 2 dB
ACR 2 dB
PSACR 2 dB
ACRF 0 dB
PSACRF 0 dB



PART NUMBER	FLAME RATING	COLOR
11074702	Plenum CMP	Blue
11074742	Plenum CMP	White
11074743	Plenum CMP	Gray
11074703	Riser CMR	Blue
11074744	Riser CMR	White
11074745	Riser CMR	Gray

LANmark-350™

Category 5e UTP
CMP OD: 0.207"
CMR OD: 0.187"
Length per box: 1,500 ft.

Electrical Characteristics
Guaranteed to 350 MHz
Characterized to 450 MHz

Guaranteed Margin to Std.
NEXT 5 dB
PSNEXT 6 dB
ACR 5 dB
PSACR 6 dB
ACRF 3 dB
PSACRF 3 dB



PART NUMBER	FLAME RATING	COLOR
11074707	Plenum CMP	Blue
11074750	Plenum CMP	White
11074751	Plenum CMP	Gray
11074708	Riser CMR	Blue
11074752	Riser CMR	White
11074753	Riser CMR	Gray

Hyper Plus 5e

Category 5e UTP
CMP OD: 0.210"
CMR OD: 0.187"
Length per box: 1,500 ft.

Electrical Characteristics
Guaranteed to 100 MHz
Characterized to 350 MHz

Guaranteed Margin to Std.
NEXT 1 dB
PSNEXT 0 dB
ACR 1 dB
PSACR 0 dB
ACRF 0 dB
PSACRF 0 dB



PART NUMBER	FLAME RATING	COLOR
11074705	Plenum CMP	Blue
11074746	Plenum CMP	White
11074747	Plenum CMP	Gray
11074706	Riser CMR	Blue
11074748	Riser CMR	White
11074749	Riser CMR	Gray

Additional colors available. Please contact Berk-Tek Inside Sales at 1-800-BERK-TEK (1-800-237-5835) for additional information.