



HIRSCHMANN

A BELDEN BRAND

Product information G 4 A 1 M MT schwarz/black

Industrial Connecting Solutions:Rectangular Connectors:DIN VDE 0627 / IEC 61984 Connectors (G serie):Cable plug:G 4 A 1 M MT schwarz/black

<http://www.e-catalog.beldensolutions.com/link/57078-24228-256261-24347-24349-36966/en/conf/ui/state>

Name	G 4 A 1 M MT schwarz/black
------	----------------------------



Press-fit surface mounted connector with solder contacts

Delivery informations

Availability	available
--------------	-----------

Product description

Description	Press-fit surface mounted connector with solder contacts
-------------	--

Type	G 4 A 1 M MT schwarz/black
------	----------------------------

Order No.	932 823-100
-----------	-------------

Type of contact	blade contacts
-----------------	----------------

Number of contacts	4
--------------------	---

Standard	DIN VDE 0627 / IEC 61984
----------	--------------------------

Housing Color	black
---------------	-------

Technical data

Pin dimensions	2.8 mm x 0.8 mm
----------------	-----------------

Rated voltage	AC/DC 50 V
---------------	------------

Rated current	10 A
---------------	------

Contact resistance	<= 4 mOhm
--------------------	-----------

Type of termination	solder
---------------------	--------

Material

Contact surface material	Sn
--------------------------	----

Contact bearer material	PA
-------------------------	----

Housing material	PA
------------------	----

Environmental conditions

Protection class (IEC 60529)	IP 65
------------------------------	-------

Pollution severity	3
--------------------	---

Temperature range	-40 °C to +90 °C
-------------------	------------------

Inflammability class

Housing	94 HB
---------	-------

Contact bearer	94 HB
----------------	-------

Approvals

VDE	VDE
-----	-----

Packing unit

Packaging unit	100 pieces
----------------	------------

Scope of delivery and accessories

Scope of delivery	1 surface mounted connector
-------------------	-----------------------------


Accessories to order separately	can be plugged into G 4 W 1 F grau, G 4 KW 1 F 2m
---------------------------------	---

Industrial Connecting Solutions: Rectangular Connectors: DIN VDE 0627 / IEC 61984 Connectors (G serie): Cable plug: G 4 A 1 M MT schwarz/black

<http://www.e-catalog.beldensolutions.com/link/57078-24228-256261-24347-24349-36966/en/conf/ui/state>

Picture

Drawing



Belden Deutschland GmbH

Im Gewerbepark 2
58579 Schalksmühle
Germany
Phone: +49 7127/14-1806
E-Mail: icos-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.