

Closet Connector Housing (CCH) Panel, pigtailed, ST[®] Compatible Connectors

Simplex, 6 F, 62.5 µm multimode (OM1)

CORNING

Corning Cable Systems Closet Connector Housing (CCH) Pigtail Panels are CCH Panels (CCH-CP) with factory terminated and tested pigtails installed. They accommodate all industry-standard connector adapter types including the LC, ST[®] Compatible, SC, SC duplex, FC and MT-RJ, as well as the keyed LC. Depending on connector type, they are available in 6-, 8-, 12-, 16-, and 24-fiber capacities. Pigtail Panels provide easier routing than Pigtail Modules when the pigtails will be routed and spliced within the same housing. Available with both ribbon and 900-µm tight buffer (MIC) cable types, each CCH Pigtail Panel is factory terminated and tested. Each module is shipped assembled with adapters and connectorized pigtails installed to the customer's specifications.

Many of our fiber optic hardware products are highly configurable. If you don't see what you are looking for here, please review the ordering matrix contained in the family spec sheet found on the right, or contact customer care at 1-800-743-2671.

Features and Benefits

Universal design approach

One-size-fits-all LANScape[®] Solutions housings

Broadest range of fiber count and adapter types

Solutions for all needs

Colored icon labeling

Easy connector identification

Specifications

General Specifications	
Application	Enterprise Networks, Data Center
Product Type	Panels & Modules
Fiber Category	62.5 µm MM (OM1)
Cable Type Stubbed	MIC [®] Cable subunit

Closet Connector Housing (CCH) Panel, pigtailed, ST® Compatible Connectors

Simplex, 6 F, 62.5 µm multimode (OM1)

CORNING

Design - Hardware

Connector Type A	ST® Compatible
Connector Polish	UPC
Fiber Count	6
Number of Adapters per Panel	6
Pigtail Length	9.84 ft (3 m)

Design Adapter

Adapter Housing Color	Beige
Adapter Housing Material	Metal
Adapter Style	Standard
Adapter Type	ST® Compatible
Insert Material	Ceramic

Design - Connector A

Housing Color	Beige
---------------	-------

Chemical Characteristics

RoHS	Free of hazardous substances according to RoHS 2002/95/EG
------	---

Ordering Information

Part Number	CCH-CP06-5T-P03KH
Product Description	Closet Connector Housing (CCH) Panel, pigtailed, ST® Compatible Connectors, Simplex, 6 F, 62.5 µm multimode (OM1)

Closet Connector Housing (CCH) Panel, pigtailed, ST[®] Compatible Connectors

Simplex, 6 F, 62.5 μm multimode (OM1)



CORNING

Shipping Information

Units per Delivery	1/1
Package Contents	CCH Adapter Panel with 3 m pigtail; installation guide



Corning Cable Systems LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/cablesystems

A complete listing of the trademarks of Corning Cable Systems is available at www.corning.com/cablesystems/trademarks.

Corning Cable Systems is ISO 9001 certified. © 2012 Corning Cable Systems. All rights reserved.



CORNING