

FDC® Unit

Capacity for (4) 6-in FDC® Connector Panels or Modules and (2) 0.4-in (Category 4R, 4S, 4A) splice trays

CORNING

Corning Cable Systems FDC® Unit product line is a family of housings combined for the splicing and termination of fiber optic cable. Designed to support both cross-connect and interconnect architectures, FDC Units can be used in a wiring center as an interface to transmission equipment or in dedicated fiber frames where test access and reconfiguration are key requirements.

FDC Units combine the benefits of connector housings and splice housings into single units. These units use standard FDC Unit panels and modules and are available in 24-, 72- and 144-fiber capacities. FDC Units are compact and modular, providing ample termination and splice storage capabilities.

To improve quality and reduce installation time of these FDC Units, Corning Cable Systems recommends factory-pigtailed connector panels or modules. Both are available with a variety of connector types and come complete with factory-installed and tested connectorized pigtails. These pigtailed units are ideal for use in FDC Units to speed the termination of fiber cable and provide the consistent quality performance of factory-installed and polished connectors.



Part Number: FDC-005-F

Features and Benefits

Available with all common industry connectors

Accepts multiple connector types in a single unit

Open design

Easier connector access

Specifications

| General Specifications | |
|------------------------|---|
| Application | Central Office, Carrier Networks, Enterprise Networks |
| Mounting Type | Rack 19-in, Rack 23-in, Wall-Mountable |
| Product Type | Rack-Mountable Hardware |

CORNING

FDC® Unit

Capacity for (4) 6-in FDC® Connector Panels or Modules and (2) 0.4-in (Category 4R, 4S, 4A) splice trays

CORNING

Design - Hardware

| | |
|----------------------|-------|
| Housing Type | FDC |
| Housing Color | Beige |
| Panel or Module Type | FDC |

Mechanical Characteristics

| | |
|--------------------|---|
| Dimensions (HxWxD) | 13.3 cm x 43.2 cm x 27.9 cm (5.25 in x 17 in x 11 in) |
|--------------------|---|

Ordering Information

| | |
|---------------------|--|
| Part Number | FDC-005-F |
| Product Description | FDC® Unit with capacity for (4) 6-in FDC Connector Panels or Modules and (2) 0.4-in (Type 4R, 4S, 4A) splice trays |

Shipping Information

| | |
|--------------------|-----|
| Units per Delivery | 1/1 |
|--------------------|-----|

Corning Cable Systems LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/cablesystems

A complete listing of the trademarks of Corning Cable Systems is available at www.corning.com/cablesystems/trademarks.

Corning Cable Systems is ISO 9001 certified. © 2012 Corning Cable Systems. All rights reserved.

CORNING