## Pretium® Wall-Mountable Housing (PWH)

Holds 2 CCH connector panels



Corning Cable Systems Pretium® Wall-Mountable Housings (PWH) provide interconnect or cross-connect capabilities between the outside plant, riser, or distribution cables and the opto-electronics and are designed to hold Plug & Play™ Universal Systems modules. Available in two, four, six and 12 panels, the rugged metal housings can be wall-mounted in main cross-connects or telecommunication rooms.

Units accept standard CCH connector panels and modules and include jumper routing guides and a bracket for securing buffer tube fan-out kits. The optional cable strain relief kit (PWHSTRNRLF-KIT) is designed for easier installation and the standoff bracket (PWH-STDOFF-BKT) extends the PWH from the wall to allow cable routing behind the housing. Brackets can also be stacked to increase the amount of space for routing. An optional field-installable lock kit is available for additional security.



#### **Features and Benefits**

#### Rugged metal construction

Durability

#### Drop-down front door

Allows for temporary workshelf

#### Jumper routing guides

Easy fiber management

#### Interconnect and cross-connect capabilities

Variety of applications

#### Field-installable lock kit (optional)

Additional security

#### Splice tray holder (optional)

Easier field splicing

### **Specifications**

General Specifications		
Application	Enterprise Networks	
Mounting Type	Wall-Mountable	
Product Type	Wall-Mountable Hardware	



# Pretium® Wall-Mountable Housing (PWH)

**Holds 2 CCH connector panels** 



Design - Hardware	
Housing Color	Gray
Housing Type	PWH
Locking Availability	Provider door
Maximum Number of Panels per Housing	2
Panel or Module Type	CCH
Splice Tray Options	2 category 2R

Mechanical Characteristics	
Dimensions (HxWxD)	23.9 cm x 44.5 cm x 10.2 cm (9.4 in x 17.5 in x 4 in)

### **Ordering Information**

Part Number	PWH-02P
Product Description	Pretium® Wall-Mountable Housing (PWH), holds 2 CCH connector panels

## **Shipping Information**

Units per Delivery	1/1
Shipping Weight	5 kg (11 lb)
Package Contents	Housing; installation guide; 2 blank panels; unit ID label; self-adhesive edge grommet 15-in; central strength member strain-relief kit; 3 1/8 x 4-in tie wraps

Corning Cable Systems LLC • PO Box 489 • Hickory, NC 28603-0489 USA 800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/cablesystems

A complete listing of the trademarks of Corning Cable Systems is available at www.corning.com/cablesystems/trademarks.

Corning Cable Systems is ISO 9001 certified. © 2012 Corning Cable Systems. All rights reserved.

