

Remote Cabinet Shelf (RCS)

1 rack unit, holds 2 FDC® connector panels

CORNING

The Remote Cabinet Shelf (RCS) is a 12- or 24-fiber patch panel designed for cabinets with limited space. In the stubbed configuration, it is ideal for installation in remote electronics cabinets. The unit's compact height allows it to mount in a single, standard EIA 19-in or 23-in rack. The unit is available for use with field-installable connectors or with preconnectorized cable.

RCS-012 occupies one (1.75 in) rack space and accommodates up to two connector panels and/or modules. RCS-024 occupies two (3.5-in) rack spaces and accommodates up to four connector panels and/or modules. Connector panels and modules are purchased separately.

The stubbed RCS contains connector panels with a specific length of preconnectorized cable installed and strain-relieved in the unit. The cable is then routed to a splice housing for termination.

Features and Benefits

Preconnectorized cable option

Reduces installation time

Variety of connector types available

Various installation options



Part Number: RCS-012



Part Number: RCS-012

Remote Cabinet Shelf (RCS)

1 rack unit, holds 2 FDC® connector panels

CORNING

Specifications

General Specifications	
Application	Central Office, Carrier Networks
Mounting Type	Rack 19-in, Rack 23-in
Product Type	Rack-Mountable Hardware

Design - Hardware	
Housing Type	RCS
Height Unit	1U
Maximum Number of Panels per Housing	2
Panel or Module Type	FDC

Mechanical Characteristics	
Dimensions (HxWxD)	4.4 cm x 43 cm x 28 cm (1.75 in x 17 in x 11 in)
Weight	2.36 kg (5.2 lb)

Ordering Information	
Part Number	RCS-012
Product Description	Remote Cabinet Shelf (RCS), 1 rack unit, holds 2 FDC® Connector Panels

Shipping Information	
Units per Delivery	1/1
Package Contents	Remote Cabinet Shelf (RCS), 1 rack unit, ships with 2 blank FDC Connector Panels, 19-in/23-in EIA mounting brackets, 23-in WECO brackets, UCC clamp kit, and mounting screws

Remote Cabinet Shelf (RCS)

1 rack unit, holds 2 FDC® connector panels

The logo consists of a solid blue square with the word "CORNING" in white, uppercase, sans-serif font centered within it.

Notes

Corning Cable Systems LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/cablesystems

A complete listing of the trademarks of Corning Cable Systems is available at www.corning.com/cablesystems/trademarks.

Corning Cable Systems is ISO 9001 certified. © 2012 Corning Cable Systems. All rights reserved.