



Aegis-10-08

### Ask For Aegis-08 By Name.

Aegis-08 telephones, by Scitec, the standard for economy branded hotels, now offers improved styling, and more features, at the same low price, plus added features like SciTouch\* One-Touch message retrieval.

#### Models

Single-line telephones

- Aegis-10-08 feature phone - 10 memory keys
- Aegis-5-08 feature telephone - 5 memory keys
- Aegis-3-08 feature telephone - 3 memory keys
- Aegis-P-08 feature telephone - no memory keys
- Aegis-LB-08 lobby telephone - no memory keys

#### Features

- Hold, Redial, Flash keys
- Dual NEON/LED message waiting light
- Programmable one-touch voice mail retrieval lightbar (Aegis-10-08/Aegis-5-08/Aegis-3-08)
- 10, 5, 3 or no programmable guest service keys
- Convenient data port
- 5 year warranty

#### Colors

- Ash
- Black



Aegis-5-08



Aegis-3-08



Aegis-P-08



Aegis-LB-08



## AEGIS-08 SERIES Single-Line Non-Speakerphones

Aegis-10-08 • Aegis-5-08 • Aegis-3-08 • Aegis-P-08

### Features & Specifications:

#### Product Identification & Order Numbers:

- Model No. Aegis-10-08 - 10 Memory Keys  
P/N 81001 (ash) / P/N 81002 (black)
- Model No. Aegis-5-08 - 5 Memory Keys  
P/N 80501 (ash) / P/N 80502 (black)
- Model No. Aegis-3-08 - 3 Memory Keys  
P/N 80301 (ash) / P/N 80302 (black)
- Model No. Aegis-P-08 - No Memory Keys  
P/N 80001 (ash) / P/N 80002 (black)
- Model No. Aegis-LB-08 - Lobby Phone  
P/N 80101 (ash) / P/N 80102 (black)

#### Product Information:

- Installation Includes
  - RJ11 Line Cords - 14ft./4.27m
  - Handset Coil Cord - 12ft/3.65m
  - Optional Wall Mount Bracket (not included)
- Line, MW, and Ringer Specifications
  - Line Voltage - Auto-Detect
  - Line Current 20mA-100mA
  - Auto-Detect for 90VDC Neon or Low Voltage LED Applications
  - Ringer Equivalence - 0.6B
- Unit Dimensions  
8.0"(l) x 6.0"(w) x 3.0"(h)
- Packaging Weight  
MasterPack Quantities of 12 Units, 31lbs/14.06kg
- Certifications  
FCC Part 68, FCC Part 15 & UL 1459 Ref.  
ADA/FCC Hearing Aid Compliant

#### Deluxe Features:

- Single Line Non-Speakerphone
- Compatible with PABX Systems
- Soft Key Technology
- Convenient Data Port
- On-Hook Pre-Dialing on Memory Keys
- Full Length Custom Tailored Faceplates
- Industrial Grade Construction with Matte Finish Design
- Non-Slip Base

#### Audio/Visual Features:

- Line Powered
- Dual NEON/LED Message Waiting Lightbar
- One-Touch Voice Mail Retrieval
- 4 Step Speaker and Handset Volume Control
- High/Low Ringer Volume Switch
- Hold Key with LED On/Off Indication
- HAC-Compatible Handset
- ADA-Compliant Volume Control

#### Programming Features:

- One-Touch Voice Mail Retrieval Lightbar (Aegis-3-08, Aegis-5-08, Aegis-10-08)
- 10, 5, 3 or No Guest Service Keys with Secure Programming
- Memory Key Entry - Maximum 32 Digits
- Flash Key
- Pause Key (submerged)
- Store Key (submerged)



Wall Mount Bracket Kit with short line cord sold separately.



5025 Galley Road  
Colorado Springs, CO 81915 USA  
+1.719.638.8821 tel  
+1.719.638.8815 fax  
info@scitecinc.com  
www.scitecinc.com

Subject to change without notice. Please refer to [www.scitecinc.com](http://www.scitecinc.com) for latest data.

© 2009 Scitec, Inc.

Scitec is a registered trademark of Scitec Inc.

Scitec Inc. is a minority-owned business.