



Aegis-10-09

Say Hello To Aegis-09.

Representing the best in today's guestroom telephones, the Aegis-09 comes with new styling and is fully equipped with our patented Sci-Touch® one-touch message retrieval light bar and an industry leading 5-year warranty.

Models

Single-line telephones

- Aegis-10-09 feature phone - 10 memory keys
- Aegis-5-09 feature telephone - 5 memory keys
- Aegis-3-09 feature telephone - 3 memory keys
- Aegis-P-09 feature telephone - no memory keys
- Aegis-LB-09 lobby telephone - no memory keys

Features

- Hold, Redial, Flash keys
- Dual NEON/LED message waiting light
- Programmable one-touch voice mail retrieval lightbar (Aegis-10-09/Aegis-5-09/Aegis-3-09)
- 10, 5, 3 or no programmable guest service keys
- Convenient data port
- 5 year warranty

Colors

- Ash
- Black



Aegis-5-09



Aegis-3-09



Aegis-P-08



Aegis-LB-09



HOSPITALITY SERIES Single-Line Non-Speakerphones

Aegis-10-09 • Aegis-5-09 • Aegis-3-09 • Aegis-P-09

Features & Specifications:

Product Identification & Order Numbers:

- Model No. Aegis-10-09 - 10 Memory Keys
P/N 98101 (ash) / P/N 98102 (black)
- Model No. Aegis-5-09 - 5 Memory Keys
P/N 98051 (ash) / P/N 98052 (black)
- Model No. Aegis-3-09 - 3 Memory Keys
P/N 98031 (ash) / P/N 98032 (black)
- Model No. Aegis-P-09 - No Memory Keys
P/N 90011 (ash) / P/N 90012 (black)
- Model No. Aegis-LB-09 - Lobby Phone
P/N 90101 (ash) / P/N 90102 (black)

Product Information:

- Installation Includes
 - RJ11 Line Cords - 14ft./4.27m
 - Handset Coil Cord - 12ft/3.65m
 - Optional Wall Mount Bracket (not included)
- Line, MW, and Ringer Specifications
 - Line Voltage - Auto-Detect
 - Line Current 20mA-100mA
 - Auto-Detect for 90VDC Neon or Low Voltage LED Applications
 - Ringer Equivalence - 0.6B
- Unit Dimensions
8.0"(l) x 6.0"(w) x 3.0"(h)
- Packaging Weight
MasterPack Quantities of 12 Units, 31lbs/14.06kg
- Certifications
FCC Part 68, FCC Part 15 & UL 1459 Ref.
ADA/FCC Hearing Aid Compliant

Deluxe Features:

- Single Line Non-Speakerphone
- Compatible with PABX Systems
- Soft Key Technology
- Convenient Data Port
- On-Hook Pre-Dialing on Memory Keys
- Full Length Custom Tailored Faceplates
- Industrial Grade Construction with Matte Finish Design
- Non-Slip Base

Audio/Visual Features:

- Line Powered
- Dual NEON/LED Message Waiting Lightbar
- One-Touch Voice Mail Retrieval
- 4 Step Speaker and Handset Volume Control
- High/Low Ringer Volume Switch
- Hold Key with LED On/Off Indication
- HAC-Compatible Handset
- ADA-Compliant Volume Control

Programming Features:

- One-Touch Voice Mail Retrieval Lightbar (Aegis-3-08, Aegis-5-08, Aegis-10-08)
- 10, 5, 3 or No Guest Service Keys with Secure Programming
- Memory Key Entry - Maximum 32 Digits
- Flash Key
- Pause Key (submerged)
- Store Key (submerged)



Wall Mount Bracket Kit with short line cord sold separately.



5025 Galley Road
Colorado Springs, CO 81915 USA
+1.719.638.8821 tel
+1.719.638.8815 fax
info@scitecinc.com
www.scitecinc.com

Subject to change without notice. Please refer to www.scitecinc.com for latest data.

© 2009 Scitec, Inc.

Scitec is a registered trademark of Scitec Inc.

Scitec Inc. is a minority-owned business.