



STANDARD SERIES Single-Line Desk, Wall, Trimline



2510DMW/ 2510D-eMW

For Demanding Environments.

Scitec industry standard 2500 sets are designed to operate in the most demanding work environments. In the office, warehouse or plant, on military bases, and local, state, and federal government properties, Scitec desk, wall, and trimlines are on the job.

Models

Single-line telephones

- 2510D desk set - double-gong bell ringer
- 2510D-e desk set - electronic ringer
- 2554 wall set - single-gong bell ringer
- 205TMW trimline - message waiting light
- 205T trimline - big button lighted dial pad

Features

- Double-gong bell ringer (2510D)
- Data port (2510D/2510D-e))
- 5 Year Warranty (2510D/2554)
- 2 Year Warranty (205TMW/205T)
- 1 Year Warranty (2510D-e)

Colors

- Ash
- Black
- White



2554MW



205TMW



205T



STANDARD SERIES Single-Line Desk, Wall, Trimline

2510D • 2554 • 205TMW • 205T

Features & Specifications:

Product Identification & Order Numbers:

- Model No. 2510D - desk set
P/N 25001 (ash) / P/N 25002 (black)
- Model No. 2510DMW - desk set
P/N 25011 (ash) / P/N 25012 (black)
- Model No. 2510D-e - desk set
P/N 25101 (ash)
- Model No. 2510D-eMW - desk set
P/N 25111 (ash)
- Model No. 2554 - wall set
P/N 25401 (ash) / P/N 25402 (black)
- Model No. 2554MW - wall set
P/N 25411 (ash) / P/N 25412 (black)
- Model No. 205TMW - trimline
P/N 20515 (white) / P/N 20501 (ash)
- Model No. 205T - trimline
P/N 20505 (white) / P/N 20501 (ash)

Product Information:

- Installation Includes
 - RJ11 Line Cords - 14ft./4.27m
 - RJ11 Line Cords - 5"/12.7cm (205TMW/205T)
 - Handset Coil Cord - 12ft/3.65m
 - Optional Wall Mount Bracket (not included)
- Line, MW, and Ringer Specifications
 - Line Voltage - Auto-Detect
 - Line Current 20mA-100mA
 - 90VDC Neon Message Waiting Indicator
 - Ringer Equivalence - 0.6B

Product Information:

- Unit Dimensions
 - 9.0"(l) x 4.5"(w) x 6.0"(h) - 2554W
 - 9.0"(l) x 7.0"(w) x 4.0"(h) - 2510D
 - 9.0"(l) x 7.0"(w) x 4.0"(h) - 2510D-e
 - 9.0"(l) x 4.0"(w) x 4.0"(h) - 205TMW/205T
- Packaging Weight
 - MasterPack Quantities of 12 Units, 31lbs/14.06kg (2554W)
 - MasterPack Quantities of 8 Units, 24lbs/10.89kg (2510D)
 - MasterPack Quantities of 16 Units, 32lbs/14.51kg (205TMW/205T)
- Certifications
 - FCC Part 68, FCC Part 15 & UL 1459 Ref.
 - ADA/FCC Hearing Aid Compliant

Telephone Features:

- Compatible with PABX Systems
- Volume Control Toggle Key (Aegis-LBE-08)
- Redial Key (205TMW/205T)
- Hold Key (205TMW/205T)
- Industrial Grade Construction with Matte or Gloss Finish Design
- Non-Slip Base

Audio/Visual Features:

- Standard Message Waiting Light (205TMW)
- Optional Message Waiting Light (2510DMW/2510D-eMW/2554MW)
- 3 Step Handset Volume Control
- RJ11 Data Port (2510D/2510D-e/205TMW/205T)
- High/Low Ringer Volume Control (not available on 2554W)
- Lighted Dial Keys (205TMW/205T))
- HAC-Compatible Handset
- ADA-Compliant Volume Control

Programming Features:

- Flash Key (205TMW/205T)



5025 Galley Road
Colorado Springs, CO 81915 USA
+1.719.638.8821 tel
+1.719.638.8815 fax
info@scitecinc.com
www.scitecinc.com

Subject to change without notice. Please refer to www.scitecinc.com for latest data.

© 2009 Scitec, Inc.

Scitec is a registered trademark of Scitec Inc.

Scitec Inc. is a minority-owned business.