











POWER L (24 V / 16 A)	DEVICE INTEGRATION WITH PANEL FEED THROUGH			
		Han® PushPull Power L, panel feed through , 5 poles, 16 A, 24 V, spring-cage connection, 0.75 – 2.5 mm <sup>2</sup> , touch-proof	Spring-cage connection, metal Spring-cage connection, plastic	09 35 431 0311 09 35 431 0331
	CONNECTOR CABLE SIDE			
		Han® PushPull Power L, connector, 5 poles, 16 A, 24 V, spring-cage connection, 0.75 – 2.5 mm <sup>2</sup> , cable diameter 9-13 mm, touch-proof	Spring-cage connection, metal Spring-cage connection, plastic	09 35 431 0401 09 35 431 0421
	ACCESSORIES			
		Han® PushPull Power L, gender changer, 5 poles, 16 A, 24 V	Gender changer Power L	09 35 431 0501
		Han® PushPull Power L, protection cover for bulkhead housing	Protection cover IP 65 / IP 67	09 35 004 5401

POWER (ACCESSORIES)	TOOLING V14			
		BUCHANAN crimping tool	Wire gauge: 0.14 – 2.5 mm <sup>2</sup>	09 99 000 0001
		Locator Han P®	for BUCHANAN crimping tool	09 99 000 0329
		Multiple crimping tool depth adjustment gauge, wire gauge: 0.5 - 1 mm <sup>2</sup> and 1.5 – 2.5 mm <sup>2</sup>	for BUCHANAN crimping tool	09 99 000 0379
		Removal tool Han P®	for Han P® contacts	09 99 000 0319
				

POWER (ACCESSORIES)	TOOLING V4			
		HARTING PushPull Power crimping tool		09 46 800 0000
		Crimping tool depth adjustment for HARTING PushPull Power crimping tool	Diameter 1.02 mm Diameter 1.15 mm	09 46 800 0002 09 46 800 0003
		Insertion tool for HARTING PushPull Power contacts	Removal tool Insertion tool	09 46 800 0098 09 46 800 0099
		Locator for HARTING PushPull Power contacts	for use with BUCHANAN crimping tool 09 99 000 0001	09 46 800 0010

ACCESSORIES	ACCESSORIES V4			
		HARTING PushPull protection covers for Hybrid, USB, RJ45, Power and LC duplex, device side, plastic	Protection cover IP 40	09 45 845 0003
			Protection cover IP 65 / IP 67, passive locking with fixing cord	09 45 845 0009
			Protection cover IP 65 / IP 67, active locking with fixing cord	09 45 845 0014
			Protection cover IP 65 / IP 67, active locking without fixing cord	09 45 845 0015
	HARTING PushPull protection covers for Hybrid, USB, RJ45, Power and LC duplex, connector, plastic	Protection cover IP 65 / IP 67, active locking with fixing cord	09 45 845 0010	

ACCESSORIES	ACCESSORIES V14			
		Han® PushPull protection cover, plastic, for RJ45, SCRJ, Power, device side	Protection cover IP 40	09 35 002 5401
			Protection cover IP 65 / IP 67	09 35 002 5402
	Han® PushPull protection cover, plastic, for RJ45, SCRJ, Power, cable side	Protection cover IP 40 Protection cover IP 65 / IP 67	09 35 002 5412 09 35 002 5411	