

TTM430 Thermal Transfer Printer

HellermannTyton's TTM430 thermal transfer printer is ideal for medium to large volume users looking for an easy to use and extremely functional thermal transfer printer. The TTM430 prints to a wide variety of materials including all of HellermannTyton's labels and ShrinkTrak. An optional cutter can cut all of the materials per label, or by the batch. The TTM430 is also both ethernet and wireless network ready, which gives the user options on placing the unit independently of the host computer. While on a network, the TTM430's status monitor (included in the driver) will alert users if the printer is out of ribbon and at the end of labels. The printer can even email the user if any of these activities occurs. Used along with TagPrint Pro, the TTM430 will offer error free printing and seamless operations.

Product Features:

- 300 dpi thermal transfer printhead
- Print speed up to 7.87"/second
- Straight through design allows easy loading of ribbon and labels (Labels are held in an interchangeable media hub)
- Larger spools or fanfold material can be fed through the back of the printer
- 64mb memory/8mb flash
- Easy to use operations and status panel
- Two adjustable gap and reflex sensors
- Lightweight/minimal foot print
- Optional cutter face plate allows labels and ShrinkTrak to be cut off after printing
- Printer status screen with date/time/network status/head temperature/ribbon amount

Printing:

- Prints on ShrinkTrak, adhesive and paper labels, and TipTags/HoleTags
- Uses standard 1" core HellermannTyton ribbons: (TT100OUT, TT822OUT, TTDTHOUT, TTHSTOUT, etc.)
- Maximum print width – 4.25" (108mm)
- Minimum print width – .24" (6mm)
- Cutter (per label, per batch) optional
- Highly accurate sensors



Specifications

Dimensions of printer	Width – 9.45" (240mm) Height – 12.28" (312mm) Depth – 17.13" (435mm)
Weight	13.2 lbs (6kg)
Power supply	100 – 240V
Operation temperature	+50°F - +95°F (+10°C - +35°C)
Print density	300dpi
Media diameter	Total diameter – 8.27" (210mm) Core diameter – 1.49" – 3.94" (38 – 100mm) Winding direction – inside or outside
Material thickness	.0028" – .014" (.07 - .35mm)
Operating System	Windows 2000/XP/Vista 32 – 64 bit/2003 32-64 bit Mac OSX 10.3 and newer Linux SUSE 9.0 CUPS based

Communications:

- Serial/USB 1.1, 2.0
- Ethernet 10/100 Base T – Interface with TCP/IP protocol. Static or Dynamic IP
- Wireless – 802.11 b/g (with optional HellermannTyton wireless card only)
- Compact flash card reader (not needed for printing)
- USB printer ports (not needed for printing)



Product Selection

Article No:	Part No:	Type:	Description:	Pkg qty:
556-00430	556-00430	TTM430	TTM430 Printer	1
556-00431	556-00431	430CFP	Cutter face plate	1
556-00432	556-00432	430WLAN	Wireless Network Card	1
556-00433	556-00433	430RLH	Label Holder	1
556-00434	556-00434	430RRH	Ribbon Holder	2
556-03065	556-03065	430RPH	Printhead	1

Labels for TTM430 Printer

To obtain information on HellermannTyton's selection of labels, view or order a product catalog by visiting www.hellermann.tyton.com/literature.asp and selecting Product Catalog.

**TagPrint^{PRO} Professional Label Creation Software**

- Beginners can use the built-in label design wizard to step through the entire label design process.
- TagPrint Pro allows the user to place graphics, text, bar codes, and lines anywhere on the label.
- All HellermannTyton marker sizes are loaded in the software for easy design and printing.



HellermannTyton

HellermannTyton North American Corporate Headquarters

7930 N. Faulkner Rd, PO Box 245017
 Milwaukee, WI 53224-9517
 Phone: (414) 355-1130, (800) 537-1512
 Fax: (414) 355-7341, (800) 848-9866
 email: corp@htamericas.com
www.hellermann.tyton.com

TS16949:2002, ISO 9001:2000, and ISO14001 Certified

© HellermannTyton Corporation
 LITPD213 — August 2008, PRINTED IN THE U.S.A.

HellermannTyton Canada

Unit #4, 205 Industrial Parkway North
 Aurora, Ontario L4G 4C4 Canada
 Phone: (800) 661-2461
 Fax: (800) 390-3904
 email: sales@hellermannntyton.ca

HellermannTyton Mexico

Anillo Periferico Sur 7980 Edificio 2 - D
 Parque Industrial Tecnológico II
 Tlaquepaque, Jalisco, Mexico 45600
 Phone: 011-52-33-3-133-9880
 Fax: 011-52-33-3-133-9861
 email: info@hellermannntyton.com.mx