

QuickPort® High-Density Die Cast Flat Patch Panel with Cable Management Bar

APPLICATION

The QuickPort High-Density Patch Panel supports 48 ports while filling only 1RU of rack space. It is available unloaded to support a variety of network requirements, and fit all industry-standard 19" racks and cabinets. An excellent choice for both retrofits and new installations, each kit includes one patch panel, labels, a label holder, and a cable management bar.



SPECIFICATION

Patch panels shall feature a 1RU/48-port design that fits industry-standard 19" equipment rack. Panels shall accommodate most QuickPort connectors. Panels shall be UL Listed. Panel shall be constructed of die-cast aluminum, and feature a durable, powder-coat finish. Label holder shall include magnification feature for port identification.

FEATURES

- 48-port density in only 1RU of rack space
- Patented design
- Robust die-cast aluminum construction
- Includes Cable Management Bar (additional bars available separately)
- Multi-color card stock for identification options
- Label holders magnify labels for easy reading

DESIGN CONSIDERATIONS

- Must follow instruction sheets included with each panel
- Panel supports 48-ports in 1RU of rack space
- Mounts on industry-standard 19" equipment rack
- Available in a variety of category ratings and will accommodate most QuickPort connectors
- Recommend jacks be terminated prior to installation in panel
- Recommend use of cable management bar to support bulk and weight of cables
- Design allows for front cable management using no additional rack space
- Empty panels available for retrofits
- Orientation of top-row connectors is rotated 180°

STANDARDS COMPLIANCE

cULus Listed

PHYSICAL SPECIFICATIONS

Dimensions: See page 2
Materials: Aluminum, powder-coated black
Capacity: 48-port

COUNTRY OF ORIGIN

USA



WARRANTY INFORMATION

For a copy of Leviton product warranties, visit www.leviton.com/warranty.



49255-D48, 49005-DMB

ELECTRONIC FILES

For CAD files, typical specs, or technical drawings (.DXF, .DWG), visit www.leviton.com.



Patch Panel



Cable Management Bar

49255-D48, 49005-DMB

PART NUMBERS

Description	Part No.
QuickPort High-Density Die Cast Flat 1RU Patch Panel (Unloaded, includes Cable Management Bar)	49255-D48
High-Density Cable Management Bar	49005-DMB



Leviton Network Solutions
 2222 - 222nd St. SE
 Bothell, WA 98021-4416

Asia / Pacific
 T +1.631.812.6228
 E infoasean@leviton.com

Canada
 T +1.514.954.1840
 E pcservice@leviton.com

Caribbean
 T +1.954.593.1896
 E infocaribbean@leviton.com

China
 T +852.2774.9876
 E infochina@leviton.com

Colombia
 T +57.1.743.6045
 E infocolombia@leviton.com

tel 1-800-824-3005
 tel +1-425-486-2222
 appeng@leviton.com
 www.leviton.com

Europe
 T +33.6.8869.1380
 E infoeurope@leviton.com

India / SAARC
 T +91.80.4322.5678
 E infoindia@leviton.com

Mexico
 T +52.55.5082.1040
 E lsamarketing@leviton.com

Middle East & Africa
 T +971.4.886.4722
 E lmeinfo@leviton.com

South Korea
 T +82.2.3273.9963
 E infokorea@leviton.com