

EZ Lite Remote® Electric Ignition System

thermOweld's EZ Lite Remote® is the latest technological advance for thermOweld® exothermic products and the entire industry! For over 50 years, thermOweld® has been developing and inventing products and practical solutions that have become "The Contractor's Choice" worldwide.

With our patented EZ Lite Remote®, the contractor, installer and distributor has versatility and ease-of-use in hand.

Use your existing thermOweld® EZ Lite® molds and weld metal you have today in your truck, at the jobsite or on your shelf!

- Use your Flint ignitor or the EZ Lite Remote® and never be stuck out on the job !
- Have 100% confidence that you will get your connections done when you want !
- Never worry about product obsolescence or dead inventory issues !
- Get it all only from thermOweld® !
- Reliable patented ignitor – 100% guarantee to ignite.
- No starting material needed.
- Use with existing thermOweld EZ Lite® molds and weld metal.
- Triple convenience features – EZ Lite® top light, side vent molds + remote option + famous standard thermOweld® weld metal reliability.
- Quick ignite – no waiting, no guessing.
- Replaceable Alkaline "D" batteries available everywhere give 100's of connections.
- Built-in Battery Life Indicator.
- Separate On/Off and Operate buttons.
- Standard six foot heat-resistant cord and connector; optional lengths available.
- Same Day Service - industry-leading jobsite supply and support, only from thermOweld®.

EZ Lite Remote® Electric Ignition Catalog #'s		Lead Time
Catalog #	Description	
38-EZLT-RU	EZ Lite Remote® Unit, ready to use with batteries installed at the factory	SDS
38-EZLT-15	EZ Lite Remote® Unit with 15 ft lead, ready to use with batteries installed at the factory	3
38-EZLT-IG	(10) 38-EZLT-IG EZ Lite Remote® Ignitors for use with existing thermOweld® EZ Lite® Molds and weld metal on your shelf, in your truck or at the job site.	SDS
38-EZLT-SK	Starter Kit complete with; (1) 38-EZLT-RU EZ Lite Remote® Unit, ready to use with batteries installed at the factory (20) 38-EZLT-IG EZ Lite Remote® Ignitors for use with existing thermOweld® EZ Lite® Molds and weld metal on your shelf, in your truck or at the job site	SDS
38-EZLT-CA	6 ft. Replacement lead	3
38-EZLT-CX	15 ft. Replacement lead	3
38-EZLT-CY	20 ft. Replacement lead	3
38-EZLT-CW	Cold Weather Kit	2



QR Code to YouTube
EZ Lite Remote® video



Patents: 7,946,466B1, 7,975,900B2, D623,261S
and patents pending

EZ Lite Remote® Electric Ignition System for thermOweld® Exothermic Welding EZ Lite Remote® Cold Weather Kit Instructions

When using thermOweld®'s EZ Lite Remote® in temperatures below 32° F (freezing) we recommend using our Cold Weather Kit (38-EZLT-CW). Below are the instructions on how to switch to the cold weather kit. The Kit includes 4 adapters and 12 AA Batteries.



Contents of Cold Weather Kit
Catalog Number 38-EZLT-CW

EZ Lite Remote® Electric Ignition System Weld Metal

Pre-packaged Weld Metal with Ignitors				
Standard	Cast Iron	Cathodic Protection	Rail	Packed per box
TW15EZ	—	TW15CPEZ	—	20
TW25EZ	TW25CIEZ	TW25CPEZ	TW25REZ	20
TW32EZ	TW32CIEZ	TW32CPEZ	TW32REZ	10
TW45EZ	TW45CIEZ	TW45CPEZ	TW45REZ	20
TW65EZ	TW65CIEZ	TW65CPEZ	TW65REZ	20
TW90EZ	TW90CIEZ	—	TW90REZ	10
TW115EZ	TW115CIEZ	—	TW115REZ	10
TW150EZ	—	—	TW150REZ	10
TW200EZ	—	—	TW200REZ	10
TW250EZ	—	—	TW250REZ	10
TW500EZ	—	—	TW500REZ	10

thermOweld® Weld Metal is sold in box quantities only




12 CM
(Weld Metal)



Call Today. Ship Today!

NOTE: thermOweld, EZ Lite & EZ Lite Remote are registered trademarks of Continental Industries.

+1 (918) 627-5210 • 1-800-558-1373 • WWW.THERMOWELD.COM