


# Communication & Low Voltage



- Permits fast and easy installation on beam flanges.
- Qwik-Latch™ cable retainer included with each hook.
- Static Load Capacity: 30 Lbs.
- Finish: Pre-galvanized

## Cable To Beam Fasteners



Communication & Low Voltage


UPC/Part Number	Catalog Number	Hook Size	Flange Thickness	Box Qty.
782051 28067	<b>BCH12-E-2-4</b>	3/4"	1/8" to 1/4"	50
782051 28072	<b>BCH12-E-5-8</b>	3/4"	5/16" to 1/2"	50
782051 28073	<b>BCH12-E-9-12</b>	3/4"	9/16" to 3/4"	50
781011 04803	<b>BCH21-E-2-4</b>	15/16"	1/8" to 1/4"	50
781011 04805	<b>BCH21-E-5-8</b>	15/16"	5/16" to 1/2"	50
781011 04807	<b>BCH21-E-9-12</b>	15/16"	9/16" to 3/4"	50
781011 04825	<b>BCH32-E-2-4</b>	2"	1/8" to 1/4"	25
781011 04827	<b>BCH32-E-5-8</b>	2"	5/16" to 1/2"	25
781011 04829	<b>BCH32-E-9-12</b>	2"	9/16" to 3/4"	25

(See pages 234-235 for technical data.)

Read safety/installation instruction sheets in packages before use.

# Communication & Low Voltage

- Permits fast and easy installation on beam flanges.
- Qwik-Latch™ cable retainer included with each hook.
- Static Load Capacity: 30 Lbs.
- Finish: Pre-galvanized



## Cable To Beam Fasteners



Allows  
360°  
Rotation




UPC/Part Number	Catalog Number	Hook Size	Flange Thickness	Box Qty.
782051 28062	<b>BCH12-U-2-4</b>	3/4"	1/8" to 1/4"	50
782051 28064	<b>BCH12-U-5-8</b>	3/4"	5/16" to 1/2"	50
782051 28066	<b>BCH12-U-9-12</b>	3/4"	9/16" to 3/4"	50
781011 04809	<b>BCH21-U-2-4</b>	15/16"	1/8" to 1/4"	50
781011 04811	<b>BCH21-U-5-8</b>	15/16"	5/16" to 1/2"	50
781011 04813	<b>BCH21-U-9-12</b>	15/16"	9/16" to 3/4"	50
781011 04831	<b>BCH32-U-2-4</b>	2"	1/8" to 1/4"	50
781011 04833	<b>BCH32-U-5-8</b>	2"	5/16" to 1/2"	50
781011 04835	<b>BCH32-U-9-12</b>	2"	9/16" to 3/4"	50
781011 04864	<b>BCH64-U-2-4</b>	4"	1/8" to 1/4"	25
781011 04865	<b>BCH64-U-5-8</b>	4"	5/16" to 1/2"	25
781011 04866	<b>BCH64-U-9-12</b>	4"	9/16" to 3/4"	25

(See pages 234-235 for technical data.)

Read safety/installation instruction sheets in packages before use.

## Communication & Low Voltage




- 360° rotation allows cable to run in any direction.
- Qwik-Latch™ cable retainer included with each hook.
- Static Load Capacity: 30 Lbs.
- Finish: Pre-galvanized

### Cable To Beam Fasteners



Communication & Low Voltage

UPC/Part Number	Catalog Number	Hook Size	Flange Thickness	Box Qty.
782051 28077	<b>BCH12-C442</b>	3/4"	1/8" to 5/8"	50
781011 04823	<b>BCH21-C442</b>	15/16"	1/8" to 5/8"	50
781011 04845	<b>BCH32-C442</b>	2"	1/8" to 5/8"	50
781011 04868	<b>BCH64-C442</b>	4"	1/8" to 5/8"	25



- 360° rotation allows cable to run in any direction.
- Qwik-Latch cable retainer included with each hook.
- Static Load Capacity: 30 Lbs.
- Finish: Pre-galvanized

### Cable To Beam Fasteners




UPC/Part Number	Catalog Number	Hook Size	Flange Thickness	Box Qty.
782051 41850	<b>BCH12-C442A</b>	3/4"	1/8" to 5/8"	50
782051 41851	<b>BCH21-C442A</b>	15/16"	1/8" to 5/8"	50
782051 41852	<b>BCH32-C442A</b>	2"	1/8" to 5/8"	50
782051 41853	<b>BCH64-C442A</b>	4"	1/8" to 5/8"	25

(See pages 234-235 for technical data.)

Read safety/installation instruction sheets in packages before use.

# Communication & Low Voltage

- 360° rotation allows cable to run in any direction.
- Qwik-Latch™ cable retainer included with each hook.
- Static Load Capacity: 30 Lbs.
- Finish: Pre-galvanized




## Cable To Beam Fasteners



Communication & Low Voltage

UPC/Part Number	Catalog Number	Hook Size	Flange Thickness	Box Qty.
782051 28074	<b>BCH12-C2</b>	3/4"	thru 1/2"	50
781011 04821	<b>BCH21-C2</b>	15/16"	thru 1/2"	50
781011 04843	<b>BCH32-C2</b>	2"	thru 1/2"	50
781011 04867	<b>BCH64-C2</b>	4"	thru 1/2"	25

- Qwik-Latch cable retainer included with each hook.
- Static Load Capacity: 30 Lbs.
- Finish: Pre-galvanized



## Cable To Beam Fasteners



UPC/Part Number	Catalog Number	Hook Size	Flange Thickness	Box Qty.
782051 41303	<b>BCH12-C1</b>	3/4"	thru 1/2"	50
781011 95578	<b>BCH21-C1</b>	15/16"	thru 1/2"	50
781011 95560	<b>BCH32-C1</b>	2"	thru 1/2"	50
782051 41304	<b>BCH64-C1</b>	4"	thru 1/2"	25

(See pages 234-235 for technical data.)

Read safety/installation instruction sheets in packages before use.