

# Fish Rods & Accessories

## Fish Rods



- Use to install wires above ceilings, through walls and under carpets and raised floors.
- 1/4" diameter fish rods are flexible, yet rigid for pulling wire long distances.
- Connect individual sections end-to-end to create a variety of lengths.
- Threaded connectors are beveled on both ends to prevent snagging and hang ups on obstructions.
- Sets contain (1 ea.) steel "bullet nose" and (1 ea.) hook accessory.
- Cat. No. 56103 also includes one 3/16" x 5' glow rod section to help guide fish rods into dark spaces.

56100

Cat. No.	Description	Set Contains	Diameter	Weight
56100	12' (3.6 m) fish rod set	(3 ea.) 1/4" x 4' (6.3 mm x 1.2 m) fish rods (1 ea.) bullet nose attachment (1 ea.) hook attachment	1/4" (6 mm)	1.2 lbs. (0.5 kg)
56101	24' (7.3 m) fish rod set	(4 ea.) 1/4" x 6' (6.3 mm x 1.8 m) fish rods (1 ea.) bullet nose attachment (1 ea.) hook attachment	1/4" (6 mm)	2.2 lbs. (1.0 kg)
56103	25' (7.6 m) fish and glow rod set	(5 ea.) 1/4" x 4' (6.3 mm x 1.2 m) fish rods (1 ea.) 3/16" x 5' (4.8 mm x 1.5 m) glow rod (1 ea.) bullet nose attachment (1 ea.) hook attachment	1/4" (6 mm)	2.7 lbs. (1.2 kg)
56111	4' (1.2 m) fish rod	-	1/4" (6 mm)	.21 lbs. (0.09 kg)
56112	6' (1.8 m) fish rod	-	1/4" (6 mm)	.28 lbs. (0.12 kg)

## Illuminated Fish Rod Tip

- Lights up for maximum visibility in dark spaces.
- Bright white, omni-directional LED light for long life.
- Tapered end for easy pushing and pulling.
- Threaded top for hook or bullet nose attachment (not included).
- Fits drilled holes as small as 5/8".
- Compatible with 1/4", 3/16" and 5/32" diameter rods.
- Replaceable batteries included.




56119

Cat. No.	Description	Dimensions	Weight
56119	illuminated fish rod tip	2.5" L x 37/64" diameter	5.0 oz. (142 g)

## Fish Rod Accessories

Cat. No.	Description	Set Contains	Weight
56104	3-piece fish and glow rod attachment set	(1 ea.) whisk attachment (1 ea.) bullet nose attachment (1 ea.) hook attachment	.2 oz. (5.7 g)
50992	hook and bullet nose replacements	n/a	.32 oz. (9.1 g)



56104

- Attachments help guide, grab, attach and steer wire or cable.
- Compatible with 1/4", 3/16", and 5/32" rod sizes.

## Extension Pole – WireSpanner™



56105

- Push/Pull wires over long spans of suspended ceilings, sub-floors, crawl spaces and attics.
- The durable 54" pole quickly and easily telescopes to a maximum of 22' long.
- Each section locks securely into place and will not spin loose or collapse.
- High quality, rigid fiberglass is sturdy, lightweight and slides easily over obstructions.
- Large capacity hook-skid tip pulls multiple wires easily and has a separate eyelet for wire tie-on.

Cat. No.	Description	Collapsed Length	Extended Length	Max. Diameter	Weight
56105	WireSpanner™ installation tool	54" (1.3 m)	22' (6.7 m)	2" (50 mm)	4 lbs. (1.8 kg)
56118	WireSpanner™ carry case	-	-	-	0.4 lbs. (0.2 kg)

All dimensions are in inches and (millimeters) unless otherwise specified.

**⚠WARNING:** Always wear approved eye protection.

**⚠WARNING:** Never remove screws while fish tape is coiled inside reel.

**⚠WARNING:** NEVER use on or near live electrical circuits.

**⚠WARNING:** Use a safe work position to avoid loss of balance.