

## Split M Block: 50-Pair

### APPLICATION

Leviton's Split M Block provides up to 50 fixed cross-connections for voice, security and data applications. Designed for entrance facilities and telecommunications closets. Mounts to walls or backboards, Category 5 rated.

### STANDARDS COMPLIANCE

Meets all applicable standards: UL listed; complies with TIA/EIA 568-B requirements and FCC Part 68.

### PHYSICAL SPECIFICATIONS

Dimensions: 10.0"H x 3.4"W x 1.2"D  
Materials: Block is made of fire-retardant plastic.

### DESIGN CONSIDERATIONS

- Compact design for space-limited applications.
- Terminate 22-26 AWG solid insulated cable or 18-19 AWG solid stripped cable.
- Mounts on wall or backboard.
- Route cable bundles adjacent to wiring base.
- Mount to Leviton 89 Stand-Off Brackets, providing space for routing cables behind each block.

### WARRANTY INFORMATION

For a copy of Leviton product warranties, log on to [www.levitonvoicedata.com/warranty](http://www.levitonvoicedata.com/warranty).

See ELECTRONIC FILES for CAD files (.DXF, .DWG, MS-DOS.EPS) on disk



For ELECTRONIC Typical Specs see (.TXT) file on disk.

### TYPICAL SPECIFICATION

The Split M Block shall provide 50 fixed cross-connections for voice, security and data applications. It shall be UL listed, comply with TIA/EIA 568-B and FCC Part 68 requirements and be made of fire-retardant plastic.

Split M Block: 50-Pair



For Technical Support Call 1-425-485-4288; in USA call 1-800-824-3005.  
Spec sheets and updates are also available at [www.levitonvoicedata.com](http://www.levitonvoicedata.com).

2222 - 222nd St. SE • Bothell, WA 98021 USA  
Tel: 1-800-722-2082 / 1-425-485-4288 • Fax: 1-425-483-5270 • Int'l Fax: 1-425-485-9170 • GSA Schedule Available.






# Split M Block: 50-Pair

**Part Number**  
**40066-M50**

.....

## DIMENSIONAL LINE ART

See ELECTRONIC FILES for CAD images  
(.DXF, .DWG, MS-DOS.EPS)



## PART NUMBERS

Description	Part No.
Split M Block; 50-Pair	40066-M50



For Technical Support Call 1-425-485-4288; in USA call 1-800-824-3005.  
Spec sheets and updates are also available at [www.levitonvoicedata.com](http://www.levitonvoicedata.com).



2222 - 222nd St. SE • Bothell, WA 98021 USA • Tel: 1-800-722-2082 / 1-425-485-4288 • Fax: 1-425-483-5270 • Int'l Fax: 1-425-485-9170 • GSA Schedule Available.