

2 POST RACKS R



In addition to standard, 84" high 2 post racks (GLRR-1984), Great Lakes also offers sizes ranging from 36"H to 108"H. Racks are still able to accept horizontal cable management and shelves, making them ideal for any amount of equipment. The following racks are not standard product. Please call [1.866.TRY.GLCC](tel:1.866.TRY.GLCC) for details and our best lead time.

PART NO.	DESCRIPTION
GLRR-1936	2 Post Rack, 36"H x 20.31"W x 14"D, wt. cap. 1500 lbs, 18 RMU, mill finish
GLRR-1936BA	2 Post Rack, 36"H x 20.31"W x 14"D, wt. cap. 1500 lbs, 18 RMU, black anodized finish
GLRR-1948	2 Post Rack, 48"H x 20.31"W x 14"D, wt. cap. 1500 lbs, 24 RMU, mill finish
GLRR-1948BA	2 Post Rack, 48"H x 20.31"W x 14"D, wt. cap. 1500 lbs, 24 RMU, black anodized finish
GLRR-1960	2 Post Rack, 60"H x 20.31"W x 14"D, wt. cap. 1500 lbs, 31 RMU, mill finish
GLRR-1960BA	2 Post Rack, 60"H x 20.31"W x 14"D, wt. cap. 1500 lbs, 31 RMU, black anodized finish
GLRR-1966	2 Post Rack, 66"H x 20.31"W x 14"D, wt. cap. 1500 lbs, 35 RMU, mill finish
GLRR-1966BA	2 Post Rack, 66"H x 20.31"W x 14"D, wt. cap. 1500 lbs, 35 RMU, black anodized finish
GLRR-1972	2 Post Rack, 72"H x 20.31"W x 14"D, wt. cap. 1500 lbs, 38 RMU, mill finish
GLRR-1972BA	2 Post Rack, 72"H x 20.31"W x 14"D, wt. cap. 1500 lbs, 38 RMU, black anodized finish
GLRR-1996	2 Post Rack, 96"H x 20.31"W x 14"D, wt. cap. 1500 lbs, 52 RMU, mill finish
GLRR-1996BA	2 Post Rack, 96"H x 20.31"W x 14"D, wt. cap. 1500 lbs, 52 RMU, black anodized finish
GLRR-19108	2 Post Rack, 108"H x 20.31"W x 14"D, wt. cap. 1500 lbs, 59 RMU, mill finish
GLRR-19108BA	2 Post Rack, 108"H x 20.31"W x 14"D, wt. cap. 1500 lbs, 59 RMU, black anodized finish

