



Southwire™

ELECTRICIAN'S TOOLS

BUILT FOR DURABILITY, RELIABILITY AND WORK.

HIGH LEVERAGE DIAGONAL CUTTING PLIERS

The high-leverage design of these Diagonal-Cutting pliers provides greater cutting power while the hot-riveted joint ensures smooth action with no handle wobble.



• SUPERIOR CUTTING POWER

Induction hardened cutting blades ensure efficient and lasting cutting surfaces for hard and soft wire

• CUTS WHAT YOU NEED

Effectively cuts most hardened wire, ACSR, bolts, screws, and nails

• SMOOTH ACTION

Hot riveted pivot joint for smooth action and no wobble

• DURABLE

Drop forged CRV steel for durability

• EASY TO USE

High-leverage design provides maximum cutting power

SOUTHWIRETOOLS.COM

1-855-SWTOOLS
(855-798-6657)

Scan code to see more
Southwire Electrician's Tools



ALSO AVAILABLE:

MAXIS®

A SOUTHWIRE BRAND

CONTRACTOR
EQUIPMENT



Southwire™
ELECTRICIAN'S TOOLS

BUILT FOR DURABILITY, RELIABILITY AND WORK.

AVAILABILITY



DCP8

- Comfort Grip



DCP8D

- Comfort Grip
- Angled Head



DCPA8

- Dipped Grip



DCPA8D

- Dipped Grip
- Angled Head

SPECIFICATIONS

MODEL #	STOCK #	DESCRIPTION	HEIGHT	WIDTH	DEPTH	WEIGHT	HEAD TYPE	HANDLE COLOR	HANDLE FINISH
DCP8D	582894	8" HI LEV DIAG CUT PLIERS HEAD DIP HANDLE	8"	2"	0.63"	9.8 oz	STANDARD	YELLOW	DIPPED GRIP
DCPA8D	582895	8" HI LEV DIAG CUT PLIER ANGL HEAD DIP HANDLE	8"	2"	0.63"	9.8 oz	ANGLED	YELLOW	DIPPED GRIP
DCP8	582772	8" HI LEV DIAGONAL CUT PLIERS	8.25"	2.25"	0.75"	11.6 oz	STANDARD	YELLOW/BLK	COMFORT GRIP
DCPA8D	582895	8" HI LEV DIAGONAL CUT PLIERS ANGLED HEAD	8.25"	2.25"	0.75"	11.6 oz	ANGLED	YELLOW/BLK	COMFORT GRIP

1-855-SWTOOLS
(855-798-6657)

SOUTHWIRETOOLS.COM

SOUTHWIRE COMPANY
ONE SOUTHWIRE DRIVE
CARROLLTON, GA 30119