

PSU-224-DC100 Universal Power Supply

www.boschsecurity.com

BOSCH

Invented for life




The PSU-224-DC100 universal power supply provides DC voltage to one or two devices requiring a total power of up to 96 W. The power supply accepts 100-240 VAC input, and outputs 24 VDC. The power supply is certified for UL safety ratings as a Class 2 power circuit. The power supply uses input and output clamps to connect the power input cable, and up to two power output cables (no cables included). The power supply is enclosed in a rugged metal housing, and is suitable for indoor and outdoor use (IP66 rated).

Certifications and approvals

Region	Certification
Europe	CE
USA	FCC + UL

Installation/configuration notes

Dimensions



Technical specifications

Output

DC voltage	24 VDC
------------	--------

	Rated current	4.0 A
	Rated power	96 W (total both outputs)
Input		
	Voltage range	100 to 240 VAC
	Frequency range	50 to 60 Hz
	AC current	1.5 A (115 VAC) 0.5 A (230 VAC)
Construction		
	Weight	1.25 kg
	Material	Casing: Aluminum extrusion; End-caps: mild steel.
	Finish	Powder coated paint RAL 9010 (Pure White)
	Cable glands	Suitable for cable diameter 4 to 8 mm
Environment		
	Water protection	IP66
	Working temperature	-30 to +50°C
	Working humidity	20 to 95% RH non- condensing
	Storage temperature	-40 to +80°C
	Storage humidity	10 to 95% RH non- condensing
Safety & EMC		
	Safety standards	EN60950-1UL60950-1EN60 950-22, IP66
	Harmonic current	Compliance to Class C (less than 75% load); EN61000-3-3
	EMS immunity	Compliance to EN61000-4-2,3,4,5,6,8,11; ENV50204, EN55024, EN61547, light industry level (surge 4KV), criteria A

Ordering information

PSU-224-DC100 Universal Power Supply

Universal Power Supply 2x24 VDC

Order number **PSU-224-DC100**

Represented by:

Americas:

Bosch Security Systems, Inc.
130 Perinton Parkway
Fairport, New York, 14450, USA
Phone: +1 800 289 0096
Fax: +1 585 223 9180
security.sales@us.bosch.com
www.boschsecurity.us

Europe, Middle East, Africa:

Bosch Security Systems B.V.
P.O. Box 80002
5617 BA Eindhoven, The Netherlands
Phone: + 31 40 2577 284
Fax: +31 40 2577 330
emea.securitysystems@bosch.com
www.boschsecurity.com

Asia-Pacific:

Robert Bosch (SEA) Pte Ltd, Security
Systems
11 Bishan Street 21
Singapore 573943
Phone: +65 6571 2808
Fax: +65 6571 2699
apr.securitysystems@bosch.com
www.boschsecurity.asia

China:

Bosch (Shanghai) Security Systems Ltd.
201 Building, No. 333 Fuquan Road
North IBP
Changning District, Shanghai
200335 China
Phone +86 21 22181111
Fax: +86 21 22182398
www.boschsecurity.com.cn

America Latina:

Robert Bosch Ltda Security Systems Division
Via Anhanguera, Km 98
CEP 13065-900
Campinas, Sao Paulo, Brazil
Phone: +55 19 2103 2860
Fax: +55 19 2103 2862
latam.boschsecurity@bosch.com
www.boschsecurity.com