

ETP-402C – Dual Button Emergency/Information Phone

Description


Model **ETP-402C** is an outdoor-rated, ADA-compliant hands-free 2-button Emergency/Information Phone for use in locations such as: parking facilities, college campuses, controlled access gates, medical centers and industrial parks.

Features

- Two buttons for both Emergency and non-Emergency calls
- Cast metal raised letter and Braille signage for ADA compliance
- Vandal resistant stainless steel faceplate and metal buttons
- Uses regular phone lines or PBX
- Phone line powered: no power supply or battery back-up needed
- Auxiliary input and outputs to integrate with CCTV, Blue Light Strobe, Scream Alert™ and other devices
- Push button once to call, then speak hands-free
- Circuit boards are conformally coated for water protection
- LED indicator for hearing impaired
- Built-in auto-dialer can dial two numbers per button: if first number doesn't answer or is busy, dials second number.
- Auto-answer allows security to monitor and initiate calls with Emergency Phone
- Options available that offer the ability to automatically identify attendant of location of calling phone by recorded message and digital display



Specifications

Construction:	12 gauge (2.8mm) #4 brushed stainless steel face plate
Dimensions:	6.81(173) W x 9.94(252) H x 2.88(73) D in(mm)
Weight:	8 lbs. (3.6kg)
Operating Temperature:	-4°F to +149°F (-20°C to +65°C)
Mounting:	Surface mounts with rear wire entry
Communication:	2-way hands-free communication
Digit Capacity:	Up to 18 digits, including pauses, for each of two phone numbers
Dialing Speed:	Approximately 10 tones per second
Power Source:	Phone line powered (requires 20mA at 24 v off-hook)
Connection:	Parallel tip and ring connected to RJ11 connector for quick installation
Circuit Protection:	Varistor lightning suppressed and full wave polarity guarded
Programming:	Non-volatile EEPROM programming can be done from any telephone. No battery back-up is needed
"On Time":	Programmable from 1-4270 minutes in 1 minute increments.
Wiring Requirements:	1 twisted-shielded pair
Compliance:	CSA Certified to UL Standard 60950 

Options & Accessories

Voice Location Identifier:	Model ETP-402CV includes the capability to record a message identifying the location of the call. Message is recorded and duration set during programming.
"EMERGENCY" Casting:	On Model ETP-402 the top button reads EMERGENCY instead of TO CALL
Mounting Extension:	Use Model ETP-SME to allow easy conduit entry
8-Line Consolidator:	Model EC-8 allows connection of up to 8 phones on one phone line while retaining ability to call each phone individually. Can also create a closed system without need for any phone lines.
Monitoring/Diagnostic	Talk-A-Lert®, model ETP-TAL , automatically polls each Emergency Phone, reports

ETP-402C – Dual Button Emergency/Information Phone

Software Package: incoming calls and keeps permanent records of all events

Dimensions

