

ETP-MT/R OP4 – Radius Emergency Phone Tower with CCTV Arm

Description

Talk-A-Phone's ETP-MT/R OP4 Emergency Phone Tower is an ideal security solution for remote and high-risk areas. Standing over eleven feet tall (including the camera arm), this vandal-resistant tower serves as a great deterrent to crime. An always-lit LED Blue Light mounted atop the tower arm provides high visibility and gives passers-by a sense of security. Emergency call can be placed with a simple push of a button. At the same time, the LED Blue Light begins to flash, attracting attention to the location. The Emergency Phone faceplate is illuminated at all times for clear visibility during the night.

Talk-A-Phone's ETP-MT/R OP4 Emergency Phone Tower includes an arm for mounting your own CCTV dome camera above the tower for general security surveillance and is often used at university and college campuses, parking facilities, shopping malls, medical centers, industrial campuses, transit facilities and remote areas.

Features

- Fixed or PTZ CCTV dome camera can be installed on the CCTV arm above the tower, giving an operator situational awareness
- Attention-getting LED Blue Light is included and mounted atop the unit. The LED Blue Light is continuously lit and flashes for duration of a call when "EMERGENCY" button is pressed to draw attention to the unit.
- Emergency Phone faceplate is illuminated at all times by an LED Panel Light
- Vandal-resistant structure and coating designed to resist extreme weather conditions
- A variety of signage, graphics and color choices are available
- Includes 1.5" NPT camera mount
- ADA-compliant

Specifications

Dimensions (W x D x H):	12.0 x 10.0 x 143.3 in. (305 x 254 x 3640 mm) with 2 in. radius corners (height includes arm and strobe)
Weight:	385 lbs. (175 kg)
Construction:	0.25 in. steel
Coating:	High-gloss, multi-layer, corrosion-inhibitive system with resistance to UV-fade and graffiti protection
Colors:	Safety Blue is standard. Available in custom colors.
Signage:	3.25 in. high reflective white "EMERGENCY" lettering with wide-angle visibility is standard. Available in custom colors, lettering and graphics.
Lighting:	<p>LED Blue Light: 209 lumens peak, 78 flashes per minute, 70% of initial lumens after 50,000 hours of operation</p> <p>LED Panel Light: Ultra bright LEDs, 50,000 hour lifetime</p>
Power:	<p>LED Blue Light: 7.8 watts, 120VAC 7.8 watts, 12-24VDC/24VAC</p> <p>LED Panel Light: 1.2 watts, 12-120VAC/DC</p>
Mounting:	Mounts into concrete foundation using included hardware (shipped in advance). Mounting options available for pre-poured parking decks.
Compliance:	CSA Certified to UL Standard 60950
Warranty:	5-year warranty on tower (2-year warranty on electronics)



ETP-MT/R OP4 – Radius Emergency Phone Tower with CCTV Arm

Options


ETP-MT/R-OP4 Configuration	Emergency Phone Options	Tower Options
Analog Connectivity	ETP-400 Series Phone	ETP-MT/R-OP4-OP2 includes a housing for mounting your own fixed CCTV camera inside the tower at average face height. ETP-MT/R-OP4-OP3 includes a Honeywell fixed day/night CCTV camera inside the tower at average face height.
IP Connectivity	VOIP-500 Series Phone	ETP-MT/R-OP4-OP-PCS includes accommodations for an ETP-CI cellular interface kit and a PCS-1 Power Charging System when only switching power is available. For use with ETP-400 series emergency phones only. ETP-CI and PCS-1 are purchased separately.

ETP-MT/R-OP4 tower includes a LED Blue Light, a LED Panel Light and an Anchor Bolt Kit. Emergency Phone is purchased separately.

Accessories

Parking Deck Mounting Kit: Order model **ETP-PDMK-4** to mount on pre-poured parking deck.

Dimensional Diagram



All dimensions are in inches and are provided for reference only.